

# PHILIPS

Bulb


LED

4W-40W

E26

Purple

046677568887



## Brighten your home with infinite possibilities.

Philips LED energy-saving colored bulbs provide instant brightness and make colors appear more vivid. Ideal for special activities and occasions.

### **Choose a simple replacement for your old bulbs**

- Similar shape and size as standard incandescent bulb

### **Choose for a sustainable solution**

- Saves up to 80% Energy

### **Light beyond illumination**

- Colored Bulbs Classic Glass

# Highlights

## Replaces standard incandescent



With its beautifully shaped design and familiar dimensions, this is a contemporary lighting, energy-saving standard LED bulb. The perfect

sustainable replacement for traditional standard incandescent bulbs.

## Saves up to 80% Energy



Enjoy the energy-savings of LEDs without sacrificing light quality. Instantly save over 80% in energy by replacing your existing incandescent or halogen bulbs

## Brilliant Colors (Glass)

Festive LED colored bulbs to decorate your home with bright colors for holidays and special occasions. Colored glass ensures high saturation for even brighter colors, for use both indoor and out.

# Specifications

## Bulb characteristics

- Intended use: Indoor/Outdoor
- Lamp shape: Non directional bulb
- Socket: E26
- Bulb Finish: Purple
- Dimmable: No
- Bulb Material: Glass

## Durability

- Number of switch cycles: 20,000
- Ambient temperature range: -4 °F to 113 °F
- Nominal lifetime: 15,000

## Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

## Extra feature/accessory incl.

- LED integrated: Yes

## Light characteristics

- Warm-up time to 60% light: 0.5 s

## Miscellaneous

- EyeComfort: Yes
- LED Innovations: EyeComfort

## Other characteristics

- EU RoHS compliant: Yes

## Packaging information

- EAN: 046677568887
- EOC: 568881
- Product title: 4A19/PER/PURPLE/G/E26/ND 4/1PF

## Power

- Power Factor (Fraction): 0.40

## Power consumption

- Power factor: 0.4
- Voltage: 120 V
- Wattage equivalent: 40
- Power: 4

### Product dimensions and weight

- Overall height: 4-3/16 inch
- Overall length: 4-3/16 inch
- Overall width: 2-3/8 inch

### Rated values

- Rated lifetime: 15,000

### Technical specifications

- Frequency: 60
- Diameter: 2-3/8 inch
- Bulb technology: LED
- Dimmable: No
- Line Frequency: 60
- Cap-Base: E26
- UL Wet/ damp/ dry location: Wet location
- can it be used in closed luminaires: No

### The bulb

- Software upgradable: No

### What's supported

- Compatible with Effects: No
- Defined support period: Not applicable
- Compatible operating systems: Not applicable
- Communication protocol: Not applicable
- Compatibility with 3rd party systems: Not applicable

### Packaging dimensions and weight

- EAN/UPC - product: 046677568887
- Net weight: 0.03 kg
- Gross weight: 0.09 kg
- Height: 17.1 cm
- Length: 6.5 cm
- Width: 7.5 cm



Issue date: 2026-05-13  
Version: 0.52

© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)