

PHILIPS

LEDtube Type A T5

LED

1200mm

5000K

G5

Dimming

046677570446



Simple T5 LED replacement for fluorescent tubes

Philips InstantFit LED tubes replace fluorescent T5 high-output tubes operated on electronic ballasts, no rewiring needed. This plastic InstantFit tube has a bright white light, extra brightness, and a long lifetime.

High quality light

- Natural day light

Choose for a sustainable solution

- You can trust what the Philips packaging is saying.

Light beyond illumination

- Instant on

Highlights

Natural day light



This bulb has a color temperature of 5000K, creating a lighting effect that is very close to that of natural daylight. Natural daylight helps with focus and making details easier to see.

No UV or IR

The beam of light is free of infra-red meaning no heat is radiated, and no ultra-violet light means that fabric and items under this light won't fade.

Instant on

Specifications

Bulb characteristics

- Intended use: Indoor
- Lamp shape: T5
- Socket: G5
- Dimmable: Yes

Bulb dimensions

- Height: 116.2 cm
- Width: 1.58 cm

Durability

- Number of switch cycles: 50,000
- Nominal lifetime: 50,000 hour(s)

Light characteristics

- Beam angle: 160 degree(s)
- Color rendering index (CRI): 82
- Color temperature: 5000 K
- Nominal luminous flux: 3500 lm
- Warm-up time to 60% light: instant full light
- Color Code: 850 | CCT of 5000K

Miscellaneous

- EyeComfort: Yes

Other characteristics

- Efficacy: 145 lm/W

Packaging information

- EAN: 046677570446
- EOC: 570440
- Product title: 24T5HO/46-850/IF35/P/DIM 10/1 FB

Power consumption

- Power factor: 0.9
- Voltage: 39-64 V
- Wattage: 24 W
- Wattage equivalent: 54 W

Product dimensions and weight

- Length: 116.2 cm

Technical specifications

- Frequency: 40-80 Hz

Packaging dimensions and weight

- EAN/UPC - product: 046677570446
- Net weight: 0.22 kg
- Gross weight: 0.29 kg
- Height: 117.5 cm
- Length: 2.4 cm
- Width: 2.4 cm
- Material number (12NC): 929001284083



Issue date: 2024-03-29
Version: 0.140

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com