

# PHILIPS

Reflector 90W  
PAR38 E26 x2

LED

3000K

900lm

11000h

046677573218



## State-of-the-art LED for the home

Philips LED PAR spot light lamp are a long lasting, energy efficient replacement for halogen spots. They have a bright white light and are ideal for general and flood lighting.

# Specifications

## General

- Suitable For Accent Lighting: Yes

## Bulb characteristics

- Intended use: Indoor/Outdoor
- Lamp shape: Directional reflector
- Socket: E26
- Dimmable: No
- Bulb Finish: Clear
- Bulb Material: Glass

## Durability

- Number of switch cycles: 50,000
- Ambient temperature range: -4 to +113 °F
- Nominal lifetime: 11,000

## Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

## Light characteristics

- Beam angle: 40 degree(s)
- Color rendering index (CRI): 90
- Color temperature: 3000 K
- Nominal luminous flux: 900 lm
- Warm-up time to 60% light: 0.5 s
- Color Code: 930 | CCT of 3000K
- Correlated Color Temperature (Nom): 3000 K
- Luminous Flux: 900 lm
- Luminous Efficacy (rated) (Nom): 90 lm/W

## Miscellaneous

- EyeComfort: Yes
- LED Innovations: EyeComfort

## Other characteristics

- EU RoHS compliant: Yes

## Packaging information

- EAN: 046677573218
- EOC: 573212
- Product title:  
10PAR38/930/G/E26/F40/ND/ULW  
T20 4/2CT

## Power

- Power Factor (Fraction): 0.7

## Power consumption

- Power factor: 0.7
- Voltage: AC 120 V
- Wattage equivalent: 90 W
- Power Consumption: 10 W

## Product dimensions and weight

- Overall height: 5-1/8 inch
- Overall length: 5-1/8 inch
- Overall width: 4-13/16 inch

## Rated values

- Rated peak intensity: 1533 cd

## Technical specifications

- Frequency: 50-60
- Dimmable: No
- Cap-Base: E26
- UL Wet/ damp/ dry location: Wet location
- can it be used in closed luminaires: Yes

## Packaging dimensions and weight

- EAN/UPC - product: 046677573218
- Net weight: 0.64 kg
- Gross weight: 0.76 kg
- Height: 20.9 cm
- Length: 13 cm
- Width: 23.5 cm



Issue date: 2025-09-13  
Version: 0.87

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)