

# PHILIPS

Filament Bulb Clear  
40W G25 E26 x2

LED


2200-2700K

350lm

15000h

Dimming

046677573348



## Experience dimmable, warm white LED light

State-of-the-art LED light bulb providing a general lighting solution for daily indoor activities. You will save on energy costs immediately and reduce the frequency of bulb replacements, without compromising on the quality of your lighting.

### High quality light

- Designed for the comfort of your eyes

### Choose for a sustainable solution

- Long life bulbs - Lasts up to 15 years

# Highlights

## Designed for the comfort of your eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get

the glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

## 15,000-hour rated average life



With a lifetime of up to 15,000 hours, you can reduce the hassle of frequently replacing your light bulbs, and enjoy a perfect lighting solution for over 15 years.

# Specifications

## Bulb characteristics

- Intended use: Indoor/Outdoor
- Lamp shape: G25
- Socket: E26
- Bulb Finish: Clear
- Dimmable: Yes
- Bulb Material: Glass

## Durability

- Number of switch cycles: 20,000
- Ambient temperature range: -4 °F to 104 °F
- Nominal lifetime: 15,000

## Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

## Extra feature/accessory incl.

- LED integrated: Yes

## Light characteristics

- Beam angle: 300
- Color rendering index (CRI): 95
- Color temperature: 2200-2700 K
- Nominal luminous flux: 350 lm
- Warm-up time to 60% light: 0.4
- Color Code: 922-927 | CCT of 2200K-2700K
- Correlated Color Temperature (Nom): 2200, 2700
- Luminous Flux: 350 lm
- Luminous Efficacy (rated) (Nom): 100

## Miscellaneous

- EyeComfort: Yes
- LED Innovations: EyeComfort
- Extra Features: Dimmable, WarmGlow

## Other characteristics

- EU RoHS compliant: Yes

## Packaging information

- EAN: 046677573348
- EOC: 573345
- Product title: 3.5G25/PER/UD/CL/G/E26/WGD 4/2FP T20

## Power

- Power Factor (Fraction): 0.7

**Power consumption**

- Power factor: 0.7
- Voltage: 120 V
- Wattage equivalent: 40
- Power: 3.5

**Product dimensions and weight**

- Overall height: 4-11/16 inch
- Overall length: 4-11/16 inch
- Overall width: 3-3/16 inch

**Rated values**

- Rated lifetime: 15,000

**Technical specifications**

- Frequency: 60
- Diameter: 3-3/16 inch
- Bulb technology: LED
- Dimmable: Only with specific dimmers
- Line Frequency: 60
- Cap-Base: E26
- UL Wet/ damp/ dry location: Wet location
- can it be used in closed luminaires: No

**The bulb**

- Software upgradable: No

**What's supported**

- Compatible with Effects: No
- Defined support period: Not applicable
- Compatible operating systems: Not applicable
- Communication protocol: Not applicable
- Compatibility with 3rd party systems: Not applicable

**Packaging dimensions and weight**

- EAN/UPC - product: 046677573348
- Net weight: 0.08 kg
- Gross weight: 0.17 kg
- Height: 20.9 cm
- Length: 9.6 cm
- Width: 18.6 cm



Issue date: 2026-06-24  
Version: 0.79

© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)