

PHILIPS

Filament Bulb Clear
75W ST19 E26 x2

LED


2200-2700K

800lm

15000h

Dimming

046677574000



State-of-the-art LED light bulb for the home

State-of-the-art LED light bulb providing a general lighting solution for daily indoor activities. You will save on energy costs immediately and reduce the frequency of bulb replacements, without compromising on the quality of your lighting.

High quality light

- True incandescent-like warm white light

Designed to be seen, looks good on and off

- Classic glass LED

Highlights

True incandescent-like warm white light



This bulb has a color temperature of 2700K, providing you with a warm, tranquil atmosphere, perfect for relaxing. This 2700K light is ideal for home lighting design.

Glass Clear Design

The look you love, the performance you expect. Classic clear glass designs that replicate the beautiful sparkling light of traditional bulbs, for a perfect fit throughout your home.

Specifications

Bulb characteristics

- Intended use: Indoor/Outdoor
- Lamp shape: Non directional bulb
- Socket: E26
- Bulb Finish: Clear
- Dimmable: Yes

Durability

- Number of switch cycles: 20,000
- Nominal lifetime: 15,000

Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- LED integrated: Yes

Light characteristics

- Beam angle: 300
- Color rendering index (CRI): 90
- Color temperature: 2200-2700 K
- Nominal luminous flux: 800 lm
- Warm-up time to 60% light: instant full light
- Color Code: 922-927 | CCT of 2200K-2700K
- Luminous Efficacy (rated) (Nom): 100

Miscellaneous

- EyeComfort: Yes
- LED Innovations: EyeComfort
- Extra Features: Decorative, Dimmable, WarmGlow

Packaging information

- EAN: 046677574000
- EOC: 574004
- Product title: 8ST19/VIN/927-922/CL/G/E26/WGD 4/2PF T20

Power consumption

- Power factor: 0.7
- Voltage: 120 V
- Wattage equivalent: 75
- Power: 8

Product dimensions and weight

- Overall height: 5-7/16 inch
- Overall length: 5-7/16 inch
- Overall width: 2-9/16 inch

Technical specifications

- Frequency: 60
- Bulb technology: LED

The bulb

- Software upgradable: No

What's supported

- Compatible with Effects: No
- Defined support period: Not applicable
- Compatible operating systems: Not applicable
- Communication protocol: Not applicable
- Compatibility with 3rd party systems: Not applicable

Packaging dimensions and weight

- EAN/UPC - product: 046677574000
- Net weight: 0.09 kg
- Gross weight: 0.15 kg
- Height: 20.4 cm
- Length: 7.1 cm
- Width: 15.6 cm



Issue date: 2026-05-13
Version: 0.78

© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com