

PHILIPS

Reflector 50W
PAR20 E26 x2

LED

2200-2700K

505lm

25000h

Dimming

046677576042



Dimmable LED spot with excellent light, the more you dim, the warmer the light

Not all LEDs dim the same. Philips dimmable LED PAR20 spot light lamp with a warm glow effect work like halogen spots by getting warmer in tone when dimmed. Other LED bulbs simply get less bright, without a cozy glow.

Choose a simple replacement for your old bulbs

- Similar shape and size as halogen reflector

Light beyond illumination

- Instant on

High quality LED light that lasts for decades

- Designed for the comfort of your eyes

Highlights

Replaces halogen spot



With its beautifully shaped design and familiar dimensions, this is a modern

lighting, LED reflector. The perfect sustainable replacement for traditional halogen reflectors.

Instant on

Designed for the comfort of your eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

Specifications

Bulb characteristics

- Intended use: Indoor
- Lamp shape: Directional reflector
- Socket: E26
- Bulb Finish: Clear
- Dimmable: Yes
- Bulb Material: Glass

Durability

- Number of switch cycles: 50,000
- Nominal lifetime: 25,000

Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Light characteristics

- Beam angle: 40 degree(s)
- Color rendering index (CRI): 95
- Color temperature: 2200-2700 K
- Nominal luminous flux: 505 lm
- Warm-up time to 60% light: 0.5
- Color Code: 922-927 | CCT of 2200K-2700K
- Luminous Efficacy (rated) (Nom): 87 lm/W

Miscellaneous

- EyeComfort: Yes
- LED Innovations: EyeComfort
- Extra Features: Dimmable, WarmGlow

Packaging information

- EAN: 046677576042
- EOC: 570846
- Product title: 5.8PAR20/PER/UD/27/G/E26/F40/WG/T 2/2PF

Power consumption

- Power factor: 0.7
- Voltage: AC 120 V
- Wattage equivalent: 50 W
- Power Consumption: 5.8 W

Product dimensions and weight

- Overall height: 3-5/16 inch
- Overall length: 3-5/16 inch
- Overall width: 2-9/16 inch

Rated values

- Rated peak intensity: 593 cd

Technical specifications

- Frequency: 50-60

Packaging dimensions and weight

- EAN/UPC – product: 046677576042
- Net weight: 0.24 kg
- Gross weight: 0.3 kg
- Height: 14.6 cm
- Length: 7 cm
- Width: 7 cm



Issue date: 2025-08-30
Version: 0.83

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com