

PHILIPS

Bulb

LED

15.5W-/W

E26

Daylight

046677576462



Enhanced plant growth in a beautiful white light

Philips LED Plant Grow lights not only optimize plant growth but also provide a beautiful, natural look for your plants. Full Spectrum White - the perfect color spectrum for growth and natural color.

Choose for a sustainable solution

- Long life bulb - Lasts up to 50 years

Light beyond illumination

- Enhanced color spectrum

High quality LED light that lasts for decades

- Light that shows true colors

Highlights

Long life bulb - Lasts up to 50 years



With a lifetime of up to 50,000 hours, you can reduce the hassle of frequently replacing your light bulbs,

and enjoy a perfect lighting solution for over 50 years.

Grow Light Spectrum

The perfect color spectrum to optimize plant growth while displaying your plants with a beautiful and natural look. Blue wavelengths help promote plant and vegetative growth.

Light that shows true colors



See the true colors of your clothes when you select an outfit from your wardrobe – you can pair a red dress and red shoes with confidence and be sure the colors match perfectly.

Specifications

Bulb characteristics

- Intended use: Indoor/Outdoor
- Lamp shape: Non directional reflector
- Socket: E26
- Dimmable: No

Durability

- Number of switch cycles: 50,000
- Nominal lifetime: 25,000

Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Light characteristics

- Beam angle: 50 degree(s)
- Color rendering index (CRI): 92
- Color temperature: 5000 K
- Nominal luminous flux: 1325 lm
- Warm-up time to 60% light: instant full light
- Color Code: 950 | CCT of 5000K
- Luminous Efficacy (rated) (Nom): 85 lm/W

Packaging information

- EAN: 046677576462
- EOC: 576462
- Product title:
15.5PAR38/LED/950/F50/ND/
GROW/T20 4/1PF

Power consumption

- Power factor: 0.9
- Voltage: 110-240 V
- Power Consumption: 15.5

Product dimensions and weight

- Overall height: 5-1/4 inch
- Overall length: 5-1/4 inch
- Overall width: 4-13/16 inch

Technical specifications

- Frequency: 50-60

Packaging dimensions and weight

- EAN/UPC - product: 046677576462
- Net weight: 0.35 kg
- Gross weight: 0.44 kg
- Height: 20.8 cm
- Length: 13 cm
- Width: 13 cm



Issue date: 2025-08-30
Version: 0.76

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com