

PHILIPS

Bulb 65W BR30 E26
x3

LED

5000K

650lm

15000h

Dimming

046677576752



Bright LED lighting with excellent light quality

It's sunlike lamp at home with perfect quality of light

Light beyond illumination

- Dimmable

High quality LED light that lasts for decades

- Designed for the comfort of your eyes

Highlights

Dimmable

This bulb can be used with most dimmers to create your desired ambience with smooth dimming to 10% of full light levels. Please check the dimmability compatibility chart to be certain that your particular dimmer can be used with this bulb.

Designed for the comfort of your eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

Specifications

Bulb characteristics

- Intended use: Indoor
- Lamp shape: Non directional reflector
- Socket: E26
- Bulb Finish: Frosted
- Dimmable: Yes
- Bulb Material: Plastic

Durability

- Number of switch cycles: 50,000
- Nominal lifetime: 15,000

Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Light characteristics

- Beam angle: 110 degree(s)
- Color rendering index (CRI): 95
- Color temperature: 5000 K
- Nominal luminous flux: 650 lm
- Warm-up time to 60% light: instant full light
- Color Code: 950 | CCT of 5000K
- Luminous Efficacy (rated) (Nom): 86 lm/W

Miscellaneous

- EyeComfort: Yes
- LED Innovations: EyeComfort
- Extra Features: Dimmable

Packaging information

- EAN: 046677576752
- EOC: 576751
- Product title: 7.5BR30/PER/UD/50/P/E26/D/T20 3/3CT

Power consumption

- Power factor: 0.7
- Voltage: 120 V
- Wattage equivalent: 65 W
- Power Consumption: 7.5 W

Product dimensions and weight

- Overall height: 5-1/8 inch
- Overall length: 5-1/8 inch
- Overall width: 3-3/4 inch

Technical specifications

- Frequency: 60

Packaging dimensions and weight

- EAN/UPC - product: 046677576752
- Net weight: 0.17 kg
- Gross weight: 0.46 kg
- Height: 17.9 cm
- Length: 9.5 cm
- Width: 18.5 cm



Issue date: 2025-08-30
Version: 0.96

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com