

# PHILIPS

Bulb 65W BR30 E26  
x3

LED

2700/3000/3500/4000/5000  
K

650lm

15000h

Dimming

046677583163



## Creative innovation to realize color selection to match your desired atmosphere

Philips LED light bulbs provide an easy solution to realize the color selection to fit for your desired application. It's designed with beautiful light, an exceptionally long life, and immediate, significant energy savings. With a pure and elegant design, this bulb is the perfect replacement for your traditional bulbs.

### Light beyond illumination

- Dimmable
- Instant on

# Highlights

## Dimmable

This bulb can be used with most dimmers to create your desired ambience with smooth dimming to 10%

of full light levels. Please check the dimmability compatibility chart to be certain that your particular dimmer can be used with this bulb.

## Instant on

# Specifications

## Bulb characteristics

- Intended use: Indoor
- Lamp shape: Non directional reflector
- Socket: E26
- Bulb Finish: Frosted
- Dimmable: Yes
- Bulb Material: Plastic

## Durability

- Number of switch cycles: 50,000
- Ambient temperature range: -4 to +113 °F
- Nominal lifetime: 15,000

## Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

## Extra feature/accessory incl.

- LED integrated: Yes

## Light characteristics

- Beam angle: 110
- Color rendering index (CRI): 90
- Color temperature: 2700-3000-3500-4000-5000 K
- Nominal luminous flux: 650 lm
- Warm-up time to 60% light: 0.5
- Correlated Color Temperature (Nom): 2700, 3000, 3500, 4000, 5000, Selectable
- Luminous Flux: 650 lm
- Luminous Efficacy (rated) (Nom): 90

## Miscellaneous

- EyeComfort: Yes
- LED Innovations: EyeComfort
- Extra Features: Dimmable

## Other characteristics

- EU RoHS compliant: Yes

## Packaging information

- EAN: 046677583163
- EOC: 583161
- Product title: 7.2BR30/DipS/5CCT/P/E26/DIM/T20 2/3CT

## Power

- Power Factor (Fraction): 0.7

## Power consumption

- Power factor: 0.7
- Voltage: AC 120 V
- Wattage equivalent: 65
- Power: 7.2

## Product dimensions and weight

- Overall height: 5-1/8 inch
- Overall length: 5-1/8 inch
- Overall width: 3-3/4 inch

## Technical specifications

- Frequency: 60
- Diameter: 3-3/4 inch
- Bulb technology: LED
- Dimmable: Only with specific dimmers
- Cap-Base: E26
- UL Wet/ damp/ dry location: Damp location
- can it be used in closed luminaires: Yes

## The bulb

- Software upgradable: No

### What's supported

- Compatible with Effects: No
- Defined support period: Not applicable
- Compatible operating systems: Not applicable
- Communication protocol: Not applicable
- Compatibility with 3rd party systems: Not applicable

### Packaging dimensions and weight

- EAN/UPC - product: 046677583163
- Net weight: 0.4 kg
- Gross weight: 0.5 kg
- Height: 17.9 cm
- Length: 9.5 cm
- Width: 18.5 cm



Issue date: 2026-06-24  
Version: 0.117

© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)