

# PHILIPS

LEDtube Type A T8

LED

1200mm

6500K

G13

046677586072



## Bright LED lighting with excellent light quality

Upgrading to Philips LED tubes is a fast and easy way to replace your old fluorescent tubes with modern and efficient LED technology. This Philips LED tube is perfect for the places that need a lot of light.

### **Choose a simple replacement for your old bulbs**

- Perfect replacement T8 linear fluorescent application
- Compatible with either T8 or T12 ballasts

# Highlights

## Similar to linear fluorescents

The perfect quick and easy replacement for T8 linear fluorescent tubes. It fits directly into standard T8 linear fluorescent G13 sockets.

## UniversalFit Ballast Compatibility

Take the guesswork out of replacing T8 or T12 fluorescent tubes. Works with either T8 or T12 ballasts.

# Specifications

## Bulb characteristics

- Intended use: Indoor
- Lamp shape: T8
- Socket: G13
- Bulb Finish: Frosted
- Dimmable: No
- Bulb Material: Glass

## Durability

- Number of switch cycles: 50,000
- Nominal lifetime: 36,000

## Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

## Extra feature/accessory incl.

- LED integrated: Yes

## Light characteristics

- Beam angle: 220
- Color rendering index (CRI): 80
- Color temperature: 6500 K
- Nominal luminous flux: 1800 lm
- Luminous Efficacy (rated) (Nom): 112

## Miscellaneous

- EyeComfort: Yes
- LED Innovations: EyeComfort

## Packaging information

- EAN: 046677586072
- EOC: 586073
- Product title: 16T8/LED/48-865/UF18/G 5/2 FB

## Power consumption

- Power factor: 0.9
- Voltage: AC 40-330 V
- Wattage equivalent: 32;40
- Power: 16

## Product dimensions and weight

- Overall height: 47-3/4 inch
- Overall length: 47-3/4 inch
- Overall width: 1-1/8 inch

## Service

- Warranty: 5 year(s)

## Technical specifications

- Frequency: 50-120K
- Bulb technology: LED

## The bulb

- Software upgradable: No

## What's supported

- Compatible with Effects: No
- Defined support period: Not applicable
- Compatible operating systems: Not applicable
- Communication protocol: Not applicable
- Compatibility with 3rd party systems: Not applicable

**Packaging dimensions and weight**

- EAN/UPC - product: 046677586072
- Net weight: 0.44 kg
- Gross weight: 0.76 kg
- Height: 122.3 cm
- Length: 6 cm
- Width: 3 cm



Issue date: 2026-05-13  
Version: 0.99

© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)