



# Bright LED lighting with excellent light quality

Upgrading to Philips LED tubes is a fast and easy way to replace your old fluorescent tubes with modern and efficient LED technology. This Philips LED tube is perfect for the places that need a lot of light.

#### Choose for a sustainable solution

· Long life bulb - Lasts up to 36 years

# Choose a simple replacement for your old fluorescents

• Designed and tested to work with a wide range of electronic ballasts in the field.

# Highlights

# 36,000 -hour rated average life

# Compatible with electronic ballast

# Specifications

#### **Bulb characteristics**

Intended use: IndoorLamp shape: T5Socket: G5

Bulb Finish: FrostedDimmable: YesBulb Material: Glass

# **Durability**

Number of switch cycles: 50,000Nominal lifetime: 36.000

#### **Environmental**

 Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

# **Light characteristics**

Beam angle: 200 degree(s)
Color rendering index (CRI): 80
Color temperature: 3000 K
Nominal luminous flux: 1000 lm
Luminous Efficacy (rated) (Nom): 125 lm/W

# Miscellaneous

EyeComfort: Yes

· LED Innovations: EyeComfort

# **Packaging information**

• EAN: 046677591823

• EOC: 591826

Product title: 8T5HE/LED/22-830/ IF10/G/DIM 10/1 FB

# **Power consumption**

• Power factor: 0.9

Voltage: AC 120-277V, 347 VWattage equivalent: 14 WPower Consumption: 8 W

# Product dimensions and weight

Overall height: 22-3/16 inch
Overall length: 22-3/16 inch
Overall width: 3/4 inch

# **Technical specifications**

• Frequency: VA5480267

· Ballast Compatibility: Type A

can it be used in closed luminaires:
 Yes

# Packaging dimensions and weight

• EAN/UPC - product: 046677591823

Gross weight: 0.09 kgHeight: 57.6 cmLength: 2.4 cmWidth: 2.4 cm

· Net weight: 0.07 kg



Issue date: 2025-09-13 Version: 0.81 © 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N V