




LED Strip Starter Kit 6.6ft + 6.6ft

Our smart WiZ LED full color strip lets you bring beautiful indirect light into your home. Simply stick the flexible strip to any surface you like – tray ceilings or under cabinets. Starter kit comes with a 2 meter strip light, controller and power driver – no additional equipment required. Can easily be trimmed for customized fit and extended up to 10 meters (extension sold separately). Wi-Fi connected, 16 million colors and adjustable from warm white to daylight.

PRODUCT HIGHLIGHTS

- Full color
- Low Voltage
- IP20/Pu-coating




Smart lighting functionalities easy to set up

Enjoy the benefits of smart features instantly, just by connecting your WiZ light to your Wi-Fi network. Control lights easily when you're away from home and scheduling lights to go on and off automatically. No need to install additional hardware such as hub or gateway!




Set up lights to follow your own schedule

Automate your smart lights to follow your daily or weekly routines. Schedule your lights to turn on in the morning or before you arrive home, and to keep them off to save energy, when they are not necessary.



Create your perfect light scene

Make your own mix of different color and white lights modes to create the perfect light ambience for your daily moment. Simply save your new Scene and select it anytime with the WiZ app or voice.




Millions of colors and changing light modes to make your day

Choose any light color you like or simply apply a dynamic light mode we designed for you. Fireplace or Ocean, for example, will help you create an amazing atmosphere and lift your mood.



Set the right ambience with tunable warm to cool white light

Choose from a wide range of energizing cool white to soft warm white light, or simply select from the preset modes such as Focus and Relax to create the best ambience for your activities.



Control smart lighting the way you like it

WiZ enables you to control smart lighting in multiple ways. Adjust lights with your smartphone, voice, the WiZ remote control, or by using the existing wall switch to toggle between two favorite modes. Works with Google Home, Alexa and Siri Shortcuts.



SPECIFICATIONS

BULB CHARACTERISTICS

Intended use: Indoor

DESIGN AND FINISHING

Color: White

Material: Plastic

DURABILITY

Average life (at 2.7 hrs/day): 15 year(s)

Lumen maintenance factor: 70%

Number of switch cycles: 50,000

Nominal lifetime: 15,000

EXTRA FEATURE/ACCESSORY INCL.

Adjustable spot head: Not adjustable

Dimmable with remote control: No

LED integrated: Yes

On/off switch on wire: Yes

Power adapter included: Yes

Remote control included: No

LIGHT CHARACTERISTICS

Color consistency: 6 SDCM

Color rendering index (CRI): ≥80

Color temperature: 2700-6500 K

Warm-up time to 60% light: 2

Luminous Efficacy (rated) (Nom): 75

lm/W

MISCELLANEOUS

Especially designed for: Living Room

Kitchen Bedroom Children's room

OTHER CHARACTERISTICS

Lamp current: 500 mA

POWER CONSUMPTION

Power factor: 0.5

Voltage: 100-120 V

Power Consumption: 20

PRODUCT DIMENSIONS AND WEIGHT

Net weight: 0.35 kg

Overall height: 1/8 inch

Overall length: 157-1/2 inch

Overall width: 1/2 inch

SERVICE

Warranty: 1 year(s)

TECHNICAL SPECIFICATIONS

Total lumen output fixture: 1800

Light color: 2700-6500 (RGB)

Fixture dimmable: Yes

Wattage bulb included: 24

IP code: IP20 | Finger-protected

Class of protection: UL non-earthed

WHAT'S SUPPORTED

Compatible with Effects: Yes

WiFi: Wireless G

Defined support period: Minimum of 60 months after introduction date

Max. number of accessories: 9999

Communication protocol: Bluetooth
WiFi (2.4GHz)

PACKAGING DIMENSIONS AND WEIGHT

EAN/UPC - product: 046677603793

Net weight: 0.34 kg

Gross weight: 0.4 kg

Height: 15.5 cm

Length: 7 cm

Width: 14 cm



© 2025 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.