



5/6 inch Retrofit Downlight 8.3W

Add tunable warm or cool white light to your living spaces with the WiZ 6-inch tunable white downlight. Use with the WiZ app or your voice to dim and brighten or use preset light modes on Wi-Fi setups.

PRODUCT HIGHLIGHTS

- Tunable white
- Fits 5"/6" opening
- IP20/Round/White



Smart lighting functionalities easy to set up

Enjoy the benefits of smart features instantly, just by connecting your WiZ light to your Wi-Fi network. Control lights easily when you're away from home and scheduling lights to go on and off automatically. No need to install additional hardware such as hub or gateway!




Control with any Matter smart home platform

This product is Matter certified, allowing easy control through Google Home, Amazon Alexa, Apple Home, or any other Matter-based smart home platform of your choice.



Exclusive SpaceSense™ light that turns on with movement

WiZ's SpaceSense technology turns your lights into motion sensors. With a minimum of two WiZ lights in a room, you can activate the SpaceSense feature in the WiZ app and have lights turn on and off automatically with motion detection. It's simple. It's SpaceSense. It's WiZ.



Monitor your energy consumption

Get an overview of the energy consumption of your lights with the WiZ app. Easily access a weekly or daily report to help you stay on top of your energy consumption at home.



Set up lights to follow your own schedule

Automate your smart lights to follow your daily or weekly routines. Schedule your lights to turn on in the morning or before you arrive home, and to keep them off to save energy, when they are not necessary.



Set the right ambience with tunable warm to cool white light

Choose from a wide range of energizing cool white to soft warm white light, or simply select from the preset modes such as Focus and Relax to create the best ambience for your activities.



SPECIFICATIONS

BULB CHARACTERISTICS

Intended use: Indoor
Dimmable: Yes

DESIGN AND FINISHING

Color: White
Material: Metal Plastic

DURABILITY

Average life (at 2.7 hrs/day): 25 year(s)
Lumen maintenance factor: 70%
Number of switch cycles: 50,000
Nominal lifetime: 25,000

EXTRA FEATURE/ACCESSORY INCL.

Adjustable spot head: Not adjustable
Dimmable with remote control: Yes
LED integrated: Yes
Remote control included: No

LIGHT CHARACTERISTICS

Beam angle: 110 degree(s)
Color rendering index (CRI): ≥ 90
Color temperature: 2700-5000 K
Warm-up time to 60% light: 2
Luminous Efficacy (rated) (Nom): 90 lm/W

MISCELLANEOUS

Especially designed for: Living Room
Kitchen Dining Room Bedroom

OTHER CHARACTERISTICS

Lamp current: 67 mA

POWER CONSUMPTION

Power factor: 0.7
Voltage: 120 V

PRODUCT DIMENSIONS AND WEIGHT

Net weight: 0.23 kg
Overall height: 2-13/16 inch
Overall length: 7-7/16 inch
Overall width: 7-7/16 inch

SERVICE

Warranty: 3 year(s)

TECHNICAL SPECIFICATIONS

Diameter: 7-7/16 inch
Total lumen output fixture: 750
Light color: 2700-5000
Wattage bulb included: 8.3
IP code: UL02 | Damp Location
Class of protection: UL non-earthed

WHAT'S SUPPORTED

Compatible with Effects: Yes
WiFi: Wireless G
Defined support period: Minimum of 60 months after introduction date
Max. number of accessories: 9999
Communication protocol: Bluetooth
WiFi (2.4GHz)

PACKAGING DIMENSIONS AND WEIGHT

EAN/UPC - product: 046677604301
Net weight: 0.23 kg
Gross weight: 0.58 kg
Height: 23.4 cm
Length: 8.8 cm
Width: 20.9 cm



© 2025 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.