




## Wall Light ELPAS

These weatherproof, elegantly designed mains voltage fixtures give an exciting new twist to the classic outdoor wall light. Install in your front garden, back garden, balcony, or porch for 400 lumens of beautiful light. Select from millions of colors, warm to cool whites, and dynamic light modes using your existing Wi-Fi.

## PRODUCT HIGHLIGHTS

- Full color
- Mains Voltage
- Weatherproof




### Instant setup for all your smart lighting

Access all smart features instantly, simply by connecting your new lights to your existing Wi-Fi. You can control lights when you're away from home and set schedules to turn them on and off automatically. All without needing to install additional hardware. Keep the controller within Wi-Fi range, and all linked lights will be fully controllable even out of Wi-Fi range.



### Control with any Matter smart home platform

This product is Matter certified, allowing easy control through Google Home, Amazon Alexa, Apple Home, or any other Matter-based smart home platform of your choice.



### Always feel safe and secure with automated outdoor lights

Schedule your outdoor lights to turn on every day before you get home, so that you can clearly see your environment and feel safe. Set your lights to turn off automatically in the morning, or when they are not necessary, and save energy.



### Create your perfect outdoor light Scene

Mix different color and white light modes to create the perfect light ambience for your perfect garden moments. Save your scene and select it anytime with app, voice or control accessory.



### Beautify your garden with millions of colors & dynamic modes

Choose from millions of light colors, from energizing cool white to soft warm white and create the best ambience for your outdoor activities. Or simply apply a preset dynamic light mode, like Ocean, Forest or Party to create an amazing atmosphere and lift the mood.



### Control your outdoor lights the way you like it

WiZ gives you many options to control your smart lights. Simply adjust lights with your smartphone or your voice from wherever you are. Works with Google Home, Alexa and Siri Shortcuts.



# SPECIFICATIONS

## BULB CHARACTERISTICS

Intended use: Outdoor  
Lamp shape: RoundRectangle

## DESIGN AND FINISHING

Color: Black  
Material: Metal Plastic

## DURABILITY

Average life (at 2.7 hrs/day): 25 year(s)  
Lumen maintenance factor: 70%  
Number of switch cycles: 50,000

## EXTRA FEATURE/ACCESSORY INCL.

Adjustable spot head: No  
Dimmable with remote control: Yes  
LED integrated: Yes  
LED lamp(s) included: Yes  
Remote control included: No

## LIGHT CHARACTERISTICS

Color consistency: 7 SDCM  
Color rendering index (CRI): 80  
Warm-up time to 60% light: <2

## MISCELLANEOUS

Especially designed for: Garden & Patio

## OTHER CHARACTERISTICS

Lamp current: 77 mA  
Efficacy: 76 lm/W

## POWER CONSUMPTION

Power factor: 0.5  
Voltage: 100-120 V

## PRODUCT DIMENSIONS AND WEIGHT

Net weight: 0.705 kg  
Height: 19.8 cm  
Length: 15.9 cm  
Width: 11.7 cm

## SERVICE

Warranty: 2 year(s)

## TECHNICAL SPECIFICATIONS

Lifetime up to: 25,000 hour(s)  
Lumen output bulb included: 950 lm  
Diameter: 109 mm  
Total lumen output fixture: 650  
Light color: 2700-5000 (RGB)  
Fixture dimmable: Wireless Dim - Do not use with dimmer  
LED: Yes  
Built in LED: Yes  
Number of bulbs: 1  
Wattage bulb included: 8.5  
Maximum wattage replacement bulb: 8.5 W  
IP code: UL03 - Wet Location (North America)  
Class of protection: UL earthed  
Light source replaceable: No



© 2025 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.

EAN:

[wizconnected.com](http://wizconnected.com)