

# PHILIPS

Filament Bulb Clear  
100W A21 E26 x2

LED

2700/3000/4000/5000/6500  
K

1500lm

15000h

Dimming

046677606206



## Selectable colour temperatures help you to make the right choice

Enjoy 5 possible light colors in one product. Change the color of your light easily with by switching the button on the product.

### High quality light

- Designed for the comfort of your eyes

### Choose a simple replacement for your old bulbs

- Perfect fit and high-quality finishing

### Dimmable (LED Lamps)

- Dimmable (LED Lamps)

# Highlights

## Designed for the comfort of your eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get the glare. Too soft and you experience flicker. Now you can gently light up

your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

### Perfect fit

With a familiar shape, these bulbs are the perfect fit for your existing fixtures. They look just like the classic light bulb.

## Dimmable (LED Lamps)



This lamp can be used with most dimmers to create your desired ambience with smooth dimming. Please check the dimmability compatibility chart to be certain that your particular dimmer can be used with this lamp.

# Specifications

## Bulb characteristics

- Intended use: Indoor
- Lamp shape: Non directional bulb
- Socket: E26
- Bulb Finish: Clear
- Dimmable: Yes
- Bulb Material: Glass

## Durability

- Number of switch cycles: 20,000
- Nominal lifetime: 15,000

## Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

## Light characteristics

- Beam angle: 300 degree(s)
- Color rendering index (CRI): 90
- Color temperature: 2700-3000-4000-5000-6500 K
- Nominal luminous flux: 1500 lm
- Luminous Efficacy (rated) (Nom): 136 lm/W

## Miscellaneous

- EyeComfort: Yes
- LED Innovations: EyeComfort
- Extra Features: Dimmable

## Packaging information

- EAN: 046677606206
- EOC: 606200
- Product title: 11A21/Dip/5CCT/CL/G/E26/DIM/T20 2PK

## Power consumption

- Energy Star Certified: No
- Power factor: 0.7
- Voltage: AC 120 V
- Wattage: 11 W
- Wattage equivalent: 100 W

**Product dimensions and weight**

- Overall height: 5-9/16 inch
- Overall length: 5-9/16 inch
- Overall width: 2-3/4 inch

**Technical specifications**

- Frequency: 60
- can it be used in closed luminaires:  
No

**Packaging dimensions and weight**

- EAN/UPC - product: 046677606206
- Net weight: 0.08 kg
- Gross weight: 0.17 kg
- Height: 18.1 cm
- Length: 8.2 cm
- Width: 15.7 cm



Issue date: 2025-09-13  
Version: 0.202

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)