

# PHILIPS

## Floor Lights 44W

Outdoor luminaires

5000K

White

Dual Brightness

046677607340



## Durable and bright

Light to enjoy outdoor moments

### Easy installation

- Easy installation

### Advanced LED light

- High quality LED light

### Designed for outdoors

- IP65 weatherproof rated

# Highlights

## Easy installation



Installing a luminaire can be sometimes difficult. With this Philips luminaire, you can be sure that high attention has been given to facilitate it and simplify it for you. You'll find clear guidance

about where you can install the product and relevant information about water-resistant IP ratings.

## High quality LED light



These LED lights use a unique technology developed by Philips. They turn on instantly and produce optimal light output that brings out the vivid colors in your garden.

## IP65 weatherproof rated

An IP rating contains two digits which refer to protection against solids, such as dust, or liquids, such as rain. IP65 means that these light fixtures are protected against water splashed from any direction and are suitable for outdoor use.

# Specifications

## Design and finishing

- Color: White
- Material: Aluminium

## Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

## Extra feature/accessory incl.

- 5 years warranty on the LED module: Yes
- Adjustable spot head: No
- LED integrated: Yes
- Motion sensor: No
- Solar Energy: No

## Light characteristics

- Color rendering index (CRI): 80

## Miscellaneous

- Especially designed for: Garden & Patio
- Style: Modern
- Type: Floor Lights
- Extra Features: Dual Brightness

## Power consumption

- Wattage: 44 W

## Product dimensions and weight

- Net weight: 1.128 kg
- Height: 12 cm
- Length: 24 cm
- Width: 16 cm

## Service

- Warranty: 1 year(s)

#### Technical specifications

- Total lumen output fixture: 4200
- Light color: 5000
- Mains power: AC 100-130
- Fixture dimmable: No
- IP code: UL03 - Wet Location (North America)
- Class of protection: Class I - Earthed
- Light source replaceable: No
- Number of light sources: 2

- UL Wet/ damp/ dry location: Wet location

#### Packaging dimensions and weight

- EAN/UPC - product: 046677607340
- Net weight: 1.13 kg
- Gross weight: 1.59 kg
- Height: 18.5 cm
- Length: 30.5 cm
- Width: 21.5 cm



Issue date: 2025-06-16  
Version: 0.132

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)