

# PHILIPS

Zyren Wall Lights  
24.5W

UltraEfficient Solar

3000K

Black

Dual Brightness;Dusk to  
Dawn;Sensor;Solar;Water  
Resistant



046677609139



## Powerful light, long lasting quality

The Philips Zyren UltraEfficient solar security light produces 4000 lumens of intense white light to illuminate your outdoor spaces at night, giving you peace of mind and an increased sense of security. A superior passive infrared (PIR) sensor offers a broad radial sensing range of 8m and a wide tangential sensing range of 16m with no blind spots. A rotatable head lets you direct the light wherever you need it, while groundbreaking UltraEfficient technology gives you 4 nights of light on one full charge. Dusk-to-dawn operation and dual brightness maximize energy savings and ensure that you always have the light you need. An IP65 rating and robust housing design with high-quality glass and crack-resistant materials make Philips Zyren suitable for virtually all weather conditions. Available in black or white, warm white light (3000 K) or daylight (5000 K).

# Specifications

## Bulb characteristics

- Dimmable: No

## Design and finishing

- Color: Black
- Material: Plastic

## Durability

- Nominal lifetime: 50,000

## Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

## Extra feature/accessory incl.

- Adjustable spot head: No
- Anti rust anti dust: Yes
- Bi-directional light beams: No
- Day-and-night sensor: Yes
- Fully weatherproof: Yes
- LED integrated: Yes
- Motion sensor: Yes
- Solar Energy: Yes
- Centerpiece: No

## Light characteristics

- Color rendering index (CRI): 80

## Miscellaneous

- Especially designed for: Garage, Garden, Patio
- Style: Contemporary
- Type: Wall Lights
- EyeComfort: No
- LED Innovations: UltraEfficient
- Extra Features: Dual Brightness, Dusk to Dawn, Sensor, Solar, Water Resistant

## Power consumption

- Power: 24.5

## Product dimensions and weight

- Net weight: 1.09 kg
- Overall height: 5/8 inch

## Service

- Warranty: 5 year(s)

## Technical specifications

- Total lumen output fixture: 4000/50
- Bulb technology: LED
- Light color: Warm white light
- Mains power: DC 8
- Class of protection: Class III - Safe Extra Low Voltage
- Light source replaceable: No
- Number of light sources: 1
- UL Wet/ damp/ dry location: Wet location

## The bulb

- Software upgradable: No

## What's supported

- Compatible with Effects: No
- Defined support period: Not applicable
- Compatible operating systems: Not applicable
- Communication protocol: Not applicable
- Compatibility with 3rd party systems: Not applicable

## Packaging dimensions and weight

- EAN/UPC - product: 046677609139
- Net weight: 1.09 kg
- Gross weight: 1.29 kg
- Height: 22 cm
- Length: 23.5 cm
- Width: 20 cm



Issue date: 2026-05-14  
Version: 0.145

© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)