

# PHILIPS

5/6 inch Recessed  
Light 8.5W

Recessed Lights

2700 / 3000 / 3500 / 4000 /  
5000K

White

Dimmable

046677609573



## Always the right shade of white

With its robust design and optimal performance, Philips LED Performance downlight is the perfect luminaire that brings quality and brightness to any home spaces. Comfortable light that's easy on your eyes.

### Easy to experience

- Hassle-free installation that does not require wiring.

### Light effect

- Adjustable color temperature
- Uniform light distribution

### Premium quality

- EyeComfort - light that's easy on the eyes

### Durability

- Long life span up to 50,000 hours

# Highlights

## Easy installation

### Adjustable color temperature

Shift seamlessly from cool white light for concentration to a more cozy glow to unwind in.


### Uniform light distribution

Throw light across your rooms in an even and uniform manner.

### Eyecomfort

Poor quality light can cause eye strain. With many of us spending time indoors, it's more important than ever to properly light your home. Our products meet stringent test criteria including flicker, strobe, glare, color rendition and dimming effects to ensure they meet EyeComfort requirements. Philips LED bulbs not only deliver comfortable light, but also stay that way for the duration of their lifespan, delivering consistent light quality, output, and color for more than a decade. Switch to light that's easy on your eyes. Your eyes will thank you.

## Long life span up to 50,000 hours



Philips LED technology extends your product's lifetime up to 50,000 hours.

# Specifications

## Bulb characteristics

- Intended use: Indoor
- Dimmable: Yes

## Design and finishing

- Color: White
- Material: Metal

## Durability

- Number of switch cycles: 25,000
- Nominal lifetime: 50,000

## Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

## Extra feature/accessory incl.

- Adjustable spot head: No
- Dimmable with remote control: No
- LED integrated: Yes
- Remote control included: No

**Light characteristics**

- Beam angle: 110
- Color consistency: 4 SDCM
- Color rendering index (CRI): 90
- Warm-up time to 60% light: <2
- Luminous Efficacy (rated) (Nom): 100

**Miscellaneous**

- Especially designed for: Kitchen, Bedroom, Dining Room, Living Room, Home Office
- Style: Contemporary
- Type: Recessed Lights
- EyeComfort: Yes
- LED Innovations: EyeComfort
- Extra Features: Dimmable

**Other characteristics**

- Lamp current: 50 mA

**Power consumption**

- Power factor: 0.7
- Power: 8.5

**Product dimensions and weight**

- Net weight: 0.28 kg
- Overall height: 1-3/8 inch

**Service**

- Warranty: 5 year(s)

**Technical specifications**

- Diameter: 7-5/16 inch
- Total lumen output fixture: 850@5000k
- Bulb technology: LED
- Light color: 2700/3000/3500/4000/5000
- Mains power: AC 120
- Class of protection: UL non-earthed
- Number of light sources: 1
- UL Wet/ damp/ dry location: Wet location

**The bulb**

- Software upgradable: No

**What's supported**

- Compatible with Effects: No
- Defined support period: Not applicable
- Compatible operating systems: Not applicable
- Communication protocol: Not applicable
- Compatibility with 3rd party systems: Not applicable

**Packaging dimensions and weight**

- EAN/UPC - product: 046677609573
- Net weight: 0.28 kg
- Gross weight: 1.29 kg
- Height: 19.4 cm
- Length: 29.2 cm
- Width: 18.8 cm



Issue date: 2026-05-18  
Version: 0.83

© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)