

PHILIPS

Smart RGBIC LED Light Strip, 5 m, Type A, Connected by WiZ

Smart LED

Multicolor light effects

Static and dynamic light modes

Versatile and cuttable



046677609832



Colors that flow

This versatile RGBIC light strip delivers dazzling multicolor effects—from chasing rainbows and smooth color fades to sparkling dynamic scenes. Set the mood in any room using a wide range of static and dynamic light modes in vibrant colors. Designed for flexibility, the strip can be cut to fit almost any space, so you can install it easily on furniture, along walls, or under cabinets (please note that cut-off pieces cannot be reattached). Easy to set up using the WiZ app and fully compatible with all Connected by WiZ products.

Easy setup

- Set up couldn't be easier
- Easy to install

Smart features

- SpaceSense motion detection
- Sync with music

Smart devices

- Matter certified

Light modes

- Multicolor light
- Vibrant color

Highlights

Set up couldn't be easier




1. Download the WIZ APP2. Switch on your light3. Connect light to Wi-Fi

Easy to install



Bend and cut to fit any space, then use the double-sided adhesive backing and mounting accessories to secure in place.

SpaceSense motion detection




Turn your lights into motion sensors using integrated SpaceSense technology, so that they switch on automatically when you enter the room—all you need are two or more Connected by WIZ lights or devices.

Sync with music



Feel the rhythm with Music Sync. Effortlessly sync your lights with your favorite tunes using the microphone on your smartphone.

Vibrant color




Choose from millions of vibrant colors to create ambient lighting to suit any mood.

Matter certified



Control your way using your preferred smart home assistant—Matter compatible for seamless integration with Alexa, Google Home, and Apple Home.

Multicolor light



This light strip can produce various colors at once for dazzling multicolor light effects, like chasing rainbows and sparkles.

Specifications

Bulb characteristics

- Intended use: Indoor
- Dimmable: Yes

Design and finishing

- Color: White
- Material: Plastic

Durability

- Average life (at 2.7 hrs/day): 15 year(s)
- Lumen maintenance factor: 70%
- Number of switch cycles: 50,000
- Nominal lifetime: 15,000

Extra feature/accessory incl.

- Dimmable with remote control: Yes
- LED integrated: Yes
- On/off switch on wire: Yes
- Power adapter included: Yes
- Remote control included: No
- Solar Energy: No
- Warm glow dimmable light: No

Light characteristics

- Color rendering index (CRI): -
- Warm-up time to 60% light: <2

Miscellaneous

- Especially designed for: Ambience

Other characteristics

- Lamp current: 290 mA

Power consumption

- Power factor: 0.5
- Voltage: 100-240 V
- Power: 13.6

Product dimensions and weight

- Net weight: 0.205 kg
- Overall height: 1/16 inch
- Overall length: 19-11/16 inch
- Overall width: 1/16 inch

Service

- Warranty: 2 year(s)

Technical specifications

- Total lumen output fixture: NA
- Bulb technology: LED
- Light color: Gradient coloured and white light (RGBICW)
- Wattage bulb included: 16
- IP code: IP20
- Class of protection: Class II - Double Insulated

The bulb

- Software upgradable: Yes

What's supported

- Compatible with Effects: Yes
- WiFi: 802.11b/g/n
- Defined support period: Minimum of 60 months after introduction date
- Max. number of accessories: 9999
- Compatible operating systems: iOS, Android
- Communication protocol: Bluetooth, Bluetooth, WiFi (2.4GHz), WiFi (2.4GHz)
- Compatibility with 3rd party systems: Alexa, Enki, Google Home, Homey, IFTTT, Matter, Samsung Smartthings, Siri Shortcuts
- Matter functionality: Via 3rd party hubs (Wi-Fi)

Packaging dimensions and weight

- EAN/UPC - product: 046677609832
- Net weight: 0.21 kg
- Gross weight: 0.3 kg
- Height: 13.7 cm
- Length: 8.2 cm
- Width: 13.9 cm



Issue date: 2026-06-24
Version: 0.87

© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com