

# PHILIPS

Gradient Floor Light,  
RGBIC LED, Connected  
by WiZ

Smart LED

Multicolor light effects

Static and dynamic light modes

Sync with TV  
(hardware required)



046677612474



## Splashes of color

Transform your space with this gradient floor light. RGBIC technology produces vibrant light effects in multiple colors at once. With a sleek, minimalist design, it looks great in any room, while customizable preset modes let you choose between dynamic animations or soft, static glows. You can even sync your light with your TV screen (syncing hardware required) or make them dance to the beat of your favorite songs.

### Easy setup

- Set up couldn't be easier

### Smart features

- SpaceSense motion detection
- Sync with music

### Smart devices

- Matter certified

### Light modes

- Smooth gradients
- Immersive lighting

### Form factor

- Stylish design


# Highlights

## Set up couldn't be easier



1. Download the WIZ APP2. Switch on your light3. Connect light to Wi-Fi

## SpaceSense motion detection



Turn your lights into motion sensors using integrated SpaceSense technology, so that they switch on automatically when you enter the room—all you need are two or more Connected by WIZ lights or devices.

## Sync with music




Feel the rhythm with Music Sync. Effortlessly sync your lights with your favorite tunes using the microphone on your smartphone.

## Matter certified




Control your way using your preferred smart home assistant—Matter compatible for seamless integration with Alexa, Google Home, and Apple Home.

## Smooth gradients



Wash the walls with multiple colors at once, blended smoothly to create beautiful light gradient effects.

## Immersive lighting



Transform your home entertainment experience by syncing your lights with music and video—syncing hardware required.

## Stylish design



This lamp's modern, minimalist style blends effortlessly into any space, bringing a touch of sophistication and elegance to your home.

# Specifications

## Bulb characteristics

- Intended use: Indoor
- Dimmable: Yes

## Design and finishing

- Color: Black
- Material: Plastic, Aluminium

## Durability

- Average life (at 2.7 hrs/day): 15 year(s)
- Lumen maintenance factor: 70%
- Number of switch cycles: 50,000
- Ambient temperature range: +14 to +104 °F
- Nominal lifetime: 15,000

## Extra feature/accessory incl.

- Adjustable spot head: No
- Choose your color: Yes
- Dimmable with remote control: Yes
- Fully weatherproof: No
- LED integrated: Yes
- On/off switch on wire: No
- Remote control included: No
- Solar Energy: No
- Warm glow dimmable light: No

## Light characteristics

- Color rendering index (CRI): ≥80
- Color temperature: 2700/6500
- Warm-up time to 60% light: <2

## Miscellaneous

- Especially designed for: Bedroom, Living Room, Children's room, Entertainment room

## Other characteristics

- Lamp current: 125 mA

## Power consumption

- Power factor: 0.45
- Voltage: 100-240 V
- Energy Consumption kWh/1000 h: 9

## Product dimensions and weight

- Net weight: 1.347 kg
- Overall length: 5-3/8 inch

## Service

- Warranty: 2 year(s)

## Technical specifications

- Frequency: 50-60
- Diameter: 3-9/16 inch
- Total lumen output fixture: NA
- Bulb technology: LED
- Light color: Gradient coloured and white light (RGBICW)
- Wattage bulb included: 9
- IP code: IP20
- Class of protection: Class II - Double Insulated

## The bulb

- Software upgradable: Yes

## What's supported

- Compatible with Effects: Yes
- WiFi: 802.11b/g/n
- Defined support period: Minimum of 60 months after introduction date
- Max. number of accessories: 9999
- Compatible operating systems: iOS, Android
- Communication protocol: Bluetooth, WiFi (2.4GHz)
- Compatibility with 3rd party systems: Alexa, Enki, Google Home, Homey, IFTTT, Matter, Samsung Smartthings, Siri Shortcuts
- Matter functionality: Via 3rd party hubs (Wi-Fi)

## Packaging dimensions and weight

- EAN/UPC - product: 046677612474
- Net weight: 1.35 kg
- Gross weight: 3.03 kg
- Height: 14.8 cm
- Length: 143.4 cm
- Width: 14.3 cm



Issue date: 2026-07-04  
Version: 0.85

© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)