

PHILIPS

Circular fluorescent

Master T5

55 W

2GX13

Warm white

871150064279025



Bright and stylish home with slim design

For a bright and stylish home with slim design

Saves energy

- Saves energy

Gives you bright light

- Vibrant experience with extra brightness

High efficacy with high lumen output

- High initial light output

Highlights

Saves energy

Bright boost

High efficient fluorescent combined with BrightBoost technology for good color rendering and extra brightness

High initial light output

High Light output provides better light quality with more brightness and allows more vibrance in home application.

Specifications

Bulb characteristics

- Socket: 2GX13
- Technology: Energy saving lamp
- Dimmable: Yes

Bulb dimensions

- Height: 305 mm
- Width: 18 mm

Durability

- Lumen maintenance factor: 0.85
- Nominal lifetime: 12,000

Light characteristics

- Color rendering index (CRI): 81
- Color temperature: 3000 K
- Nominal luminous flux: 4210 lm
- Correlated Color Temperature (Nom): 3000 K
- Luminous Flux: 4,210 lm
- Luminous Efficacy (rated) (Nom): 76 lm/W

Power consumption

- Voltage: 230 V
- Energy Efficiency Label (EEL): G
- Power Consumption: 55.7
- Energy Consumption kWh/1000 h: 56

Technical specifications

- Frequency: 50
- Shape: Circular
- Chromaticity Coordinate Y: 0.403
- Chromaticity Coordinate X: 0.44
- EPREL Registration Number: 423622
- Flux measurement reference: Sphere
- Dimmable: Yes
- Cap-Base: 2GX13



Issue date: 2025-08-30
Version: 0.827

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com