



Chloride new Value+ LED Selectable Exit Sign (VES) combines a sleek, low-profile design with high-performance LEDs, making it a refined yet versatile choice for any general-purpose application. Featuring a convenient on-site selector switch, the VES can be easily configured to display in either red or green — eliminating the need to stock separate units. Powered by long-life LEDs, it offers consistent, dependable illumination — a smart choice for spaces where quality and style go hand in hand.

Project: _____

Location: _____

Cat.No: _____

Type: _____

Lamps: _____ Qty: _____

Notes: _____

Value+ Selectable exit sign – ordering guide

Model Number	Letter Color	Single/Double	Operation	Housing Color
VESW	Selectable Red/Green	Universal	AC only	White
VESWEM	Selectable Red/Green		Emergency	White

Accessories (order separately)

Model Number	Letter Color
WG4	Wire guard
VEPMC	Pendant mount canopy, white, (requires stem assembly).
CXPA12W	Pendant assembly, Rigid canopy, 12" white stem (requires VEPMC).
CXPAS12W	Pendant assembly, Swivel white canopy, 12" white stem (requires VEPMC).
PVS2	Polycarbonate shield

Stem lengths available: 18" 24", 30", 36", 48", and 60"

Specifications

Lamp:

- Selectable bright red/green energy efficient LED lamps.
- Uniform 6" letter illumination (3/4" stroke).

Electrical:

- Input voltage: 120/277VAC, 60Hz
- Input Power: 3W
- Battery low voltage protection
- Solid-state transfer circuit

Battery:

- Maintenance-free, rechargeable Ni-Cad battery
- Provides 90 minutes of emergency illumination
- Standard manual test switch and charge rate indicator

Codes and compliance:

- UL 924
- NFPA 70 (National Electric Code)
- NFPA 101 (Life Safety Code)
- CEC title 20
- Suitable for damp location
- Suitable for 10°C ~ 40°C (50 ~ 104°F) ambient temperature

Warranty:

- Three-year limited warranty on electronics, LEDs and battery

VES Value+ LED Selectable Exit Sign

Economy grade

Specifications

Construction:

- Injection-molded thermoplastic housing
- Plastic enclosure with 5VA flame retardant
- Compact and decorative design with easy replacement pictogram design
- Suitable for wall, side and ceiling mounting
- Universal J-Box mounting pattern on backplate
- Pop-out chevron directional indicators are easily removed when required
- All exits are provided with an extra stencil face plate for double face sign applications

Surface Dimensions

