

PHILIPS

Incandescent lamp

Incandescent reflector
lamp

60 W

Frosted

E27 cap

871150004366578



Coloured pressed-glass reflector

Coloured PAR is designed for festive illumination as well as restaurants, dance halls, discotheques, fountains and 'Son et Lumiere' spectacles. Pressed-glass and waterproof construction make this lamp ideal for indoor & outdoor use.

Not suitable for household room illumination

- For decorative color effects

Brilliant colors

- Superior coating

Suitable for both indoor & outdoor applications

- Weatherproof coloured coating

Highlights

For decorative color effects

Rich saturated colors to enhance the atmosphere

Superior coating

Weatherproof coloured coating

Specifications

Bulb characteristics

- Socket: E27
- Bulb Finish: Frosted
- Dimmable: Yes

Bulb dimensions

- Height: 104.5 mm
- Width: 63 mm

Durability

- Nominal lifetime: 1,000

Light characteristics

- Application: Accent light
- Color rendering index (CRI): 100

Luminaire fit

- Shape: NR63
- Voltage: 230 V

Power consumption

- Power Consumption: 60

Rated values

- Rated lifetime: 1,000

Technical specifications

- Dimmable: Yes
- Cap-Base: E27

Packaging dimensions and weight

- EAN/UPC - product: 8711500043665
- Net weight: 25.97 g
- Gross weight: 38.17 g
- Height: 10.5 cm
- Length: 6.2 cm
- Width: 6.2 cm



Issue date: 2025-09-17
Version: 0.743

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com