

# PHILIPS

Bulb 160W A80 B22

LED

6500K

2300lm

10000h

8718699640613



## State-of-the-art LED light bulb for the home

Philips LED light bulbs provide a beautiful, warm white light, a long lifetime, and immediate, significant energy savings. With its modern and elegant design, this dimmable bulb is the perfect replacement for your frosted traditional bulbs.

### High quality light

- No visible flicker

### Choose for a sustainable solution

- You can trust what the Philips packaging is saying.

### Designed to be seen, looks good on and off

- Looks good on and off

# Highlights

## No visible flicker

When your light flickers in quick succession it could be hard on the eyes, cause headaches, and even set off an attack for those with photosensitive epilepsy. It's both unpleasant and unnecessary. LEDs can flicker because of their rapid response to the driver current. However, because Philips LEDs are designed so that variations in your driver current's output are minimized, they eliminate

the factors that cause flicker. So, you won't see it, not even a hint.

## No UV or IR

The beam of light is free of infra-red meaning no heat is radiated, and no ultra-violet light means that fabric and items under this light won't fade.

## Looks good on and off



"These beautiful lamp with visible filament add a sense of style and nostalgia to any room. Looks good on and off."

# Specifications

## Bulb characteristics

- Intended use: Indoor
- Lamp shape: Non directional bulb
- Socket: B22
- Dimmable: No
- Bulb Finish: Frosted
- Bulb Material: Plastic

## Durability

- Number of switch cycles: 50,000
- Ambient temperature range: -20 to +45 °C
- Nominal lifetime: 12,000

## Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

## Light characteristics

- Beam angle: 150 degree(s)
- Color rendering index (CRI): 80
- Color temperature: 6500 K
- Nominal luminous flux: 2300 lm
- Warm-up time to 60% light: 0.5 s
- Correlated Color Temperature (Nom): 6500 K
- Luminous Flux: 2,300 lm
- Luminous Efficacy (rated) (Nom): 121 lm/W

## Miscellaneous

- EyeComfort: No

## Other characteristics

- EU RoHS compliant: Yes

## Packaging information

- EAN: 8718699640613
- EOC: 871869964061300
- Product title: LEDBulb 19W B22 6500K 230VA80 1CT/6APR

## Power

- Power Factor (Fraction): 0.51

#### Power consumption

- Power factor: 0.51
- Voltage: 220–240 V
- Wattage equivalent: 160(160W for Incandescent;35W CFL) W
- Power Consumption: 19 W
- Energy Consumption kWh/1000 h: 19

#### Product dimensions and weight

- Overall height: 155 mm
- Overall length: 155 mm
- Overall width: 80 mm

#### Rated values

- Rated lifetime: 12,000
- Rated peak intensity: N/A cd

#### Technical specifications

- Frequency: 50–60
- Diameter: 80 mm
- Dimmable: No
- Cap-Base: B22



Issue date: 2025-09-24  
Version: 0.159

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)