



# Durable LED accent lighting with a focused bright beam

Philips LED spots provide a focused bright beam, an exceptionally long life, and significant energy savings. This spot is the perfect long-lasting replacement for 50W spots with a GU10 cap.

#### Choose for a sustainable solution

· Safe for any room and convenient to recycle

### Create the right light for your home

Perfect for accent lighting

# Highlights

#### No hazardous substances

Philips LED lights contain absolutely no hazardous materials, making them safe for any room and convenient to recycle.

## Perfect for accent lighting



Modern lighting with a familiar wide angle light output (36 degrees), this LED spot is suitable for both accent lighting and general purpose lighting. It can be used in recessed cans and track light fixtures, and is ideal for use in kitchens, kitchen island lighting, living rooms and dining rooms.

# Specifications

#### **Bulb characteristics**

· Intended use: Indoor

· Lamp shape: Directional reflector

Socket: GU10Dimmable: No

#### **Bulb dimensions**

Height: 5.4 cmWidth: 5 cm

#### **Durability**

Number of switch cycles: 50,000Nominal lifetime: 10,000 hour(s)

#### **Environmental**

• Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

# **Light characteristics**

full light

Beam angle: 36 degree(s)
Color rendering index (CRI): 80
Color temperature: 2700 K
Nominal luminous flux: 300 lm
Warm-up time to 60% light: instant

#### Miscellaneous

· EyeComfort: No

#### Other characteristics

· Efficacy: 106 lm/W

#### **Packaging information**

• EAN: 8718699659288 • EOC: 871869965928800

Product title: Essential LED 3.2-50W

GU10 827 36D1PF/10

#### **Power consumption**

Power factor: 0.4Voltage: 220-230 VWattage: 3.2 W

Wattage equivalent: 50 W

#### Product dimensions and weight

· Length: 5.4 cm

#### **Rated values**

· Rated peak intensity: 600 cd

## **Technical specifications**

• Frequency: 50 Hz



Issue date: 2024-11-22 Version: 0.23 © 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips