



8718699755720



Create the perfect ambience with high quality dimmable light.

Create the perfect mood with Philips LED Dimmable recessed spots, you can easily dim your lights from everyday bright light to cozy tones.

Match your interior

· Decorative metallic finishing

Light effect

· Bright and focused beam

Safety

· Moisture resistance

Premium quality

• EyeComfort - light that's easy on the eyes

Control

Dimmable

Durability

· Long life span up to 15,000 hours

Highlights

Decorative metallic finishing

Contemporary metallic finishing adds a modern touch.

Bright and focused beam

Focus light on objects, a dining table or other interiors to draw attention to particular stylings.

Moisture resistance

Moisture resistance means you can confidently use this product in bathrooms, kitchens, balconies and other spaces where moisture may be a consideration.

Eyecomfort

Poor quality light can cause eye strain. With many of us spending time indoors, it's more important than ever to properly light your home. Our products meet stringent test criteria including flicker, strobe, glare, color rendition and dimming effects to ensure they

meet EyeComfort requirements. Philip s LED bulbs not only deliver comfortable light, but also stay that way for the duration of their lifespan, delivering consistent light quality, output, and color for more than a

decade. Switch to light that's easy on your eyes. Your eyes will thank you.

Dimmable

Allows you to change the mood by reducing LED brightness levels, from bright white light, to a cozy glow - just like traditional lamps.

Long life span up to 15,000 hours

Philips LED technology extends your product's lifetime up to 15,000 hours.

Specifications

Bulb characteristics

· Intended use: Indoor

Design and finishing

· Color: White

· Material: Metal, Plastic

Durability

• Number of switch cycles: 10,000

· Nominal lifetime: 20,000

Environmental

• Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- · Adjustable spot head: Not adjustable
- · Dimmable with remote control: No
- · LED integrated: Yes
- · Remote control included: No

Light characteristics

- Beam angle: 36 degree(s)
- · Color consistency: 6 SDCM
- · Color rendering index (CRI): 80
- · Color temperature: 2700 K
- Luminous Efficacy (rated) (Nom): 58 lm/W

Miscellaneous

- Especially designed for: Bathroom, Bedroom, Living Room, Dining Room, Kitchen, Office
- Style: Contemporary
- Type: Recessed Lights
- EyeComfort: Yes
- Extra Features: Dimmable, Water Resistant

Other characteristics

· Lamp current: 31 mA

Product dimensions and weight

- Net weight: 0.114 kg
- · Recessed distance: 15 mm
- Overall height: 55 mm
- · Overall length: 85 mm
- · Overall width: 85 mm
- Recessed Ceiling cutout: 7.0 cm x 7.0 cm

Service

• Warranty: 2 year(s)

Technical specifications

· Diameter: 85 mm

· Total lumen output fixture: 350

• Light color: 2700

Mains power: AC 220-240
Fixture dimmable: Yes
Wattage bulb included: 5.5
IP code: IP65 | Dust-tight and jet-proof, IP20 | Finger-protected

· Class of protection: Class II - Double

Insulated



© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not

reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips

NV

Issue date: 2025-09-03

Version: 0.320