



# Create the perfect ambience with high quality dimmable light.

Create the perfect mood with Philips LED Dimmable recessed spots, you can easily dim your lights from everyday bright light to cozy tones.

#### Easy to experience

 Choose how and where light falls with these adjustable modular lights.

# **Light effect**

· Bright and focused beam

## **Premium quality**

• EyeComfort - light that's easy on the eyes

# Control

Dimmable

# **Durability**

· Long life span up to 15,000 hours

# Highlights

# Adjustable modular light Bright and focused beam

Focus light on objects, a dining table or other interiors to draw attention to particular stylings.

#### **Evecomfort**

Poor quality light can cause eye strain. With many of us spending time indoors, it's more important than ever to properly light your home. Our products meet stringent test criteria including flicker, strobe, glare, color rendition and dimming effects to ensure they meet EyeComfort requirements. Philip s LED bulbs not only deliver comfortable light, but also stay that way for the duration of their lifespan, delivering consistent light quality, output, and color for more than a decade. Switch to light that's easy on your eyes. Your eyes will thank you.

#### **Dimmable**

Allows you to change the mood by reducing LED brightness levels, from bright white light, to a cozy glow - just like traditional lamps.

#### Long life span up to 15,000 hours

Philips LED technology extends your product's lifetime up to 15,000 hours.

# Specifications

#### **Bulb characteristics**

· Intended use: Indoor

# Design and finishing

- Color: Nickel
- · Material: Metal, Plastic

#### **Durability**

- Number of switch cycles: 10,000
- · Nominal lifetime: 20,000

# **Environmental**

 Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

#### Extra feature/accessory incl.

- Adjustable spot head: Adjustable rise and fall
- Dimmable with remote control: No
- LED integrated: Yes
- · Remote control included: No

#### **Light characteristics**

- Beam angle: 36 degree(s)
- · Color consistency: 6 SDCM
- Color rendering index (CRI): 80
- · Color temperature: 2700 K
- Luminous Efficacy (rated) (Nom): 58 lm/W

#### Miscellaneous

- Especially designed for: Bedroom, Living Room, Dining Room, Kitchen, Office
- Style: Contemporary
- Type: Recessed Lights
- EyeComfort: Yes
- Extra Features: Dimmable

## Other characteristics

· Lamp current: 31 mA

## Product dimensions and weight

Net weight: 0.118 kg
Recessed distance: 15 mm
Overall height: 55 mm
Overall length: 85 mm
Overall width: 85 mm

 $\boldsymbol{\cdot}$  Recessed Ceiling cutout: 7.0 cm x 7.0

cm

#### Service

• Warranty: 2 year(s)

# **Technical specifications**

• Diameter: 85 mm

· Total lumen output fixture: 350

· Light color: 2700

Mains power: AC 220-240
Fixture dimmable: Yes
Wattage bulb included: 5.5
IP code: IP20 | Finger-protected
Class of protection: Class II - Double

Insulated



Issue date: 2025-09-03 Version: 0.299 © 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.