PHILIPS

Filament Bulb Pink 25W G93 E27

LED

1800K

250lm

15000h

Dimming



8719514269552



A light bulb like no other

Philips LED light bulbs provide a beautiful, warm white light, an exceptionally long life, and immediate, significant energy savings. With a pure and elegant design, this bulb is the perfect replacement for your frosted traditional bulbs.

Light beyond illumination

· Vintage style, modern LED technology

High quality LED light that lasts for decades

Designed for the comfort of your eyes

Designed to be seen, looks good on and off

· Looks good on and off

Highlights

Vintage style, modern LED

LED Classic bulbs are based on standard LED energy-saving technology. Now you can enjoy a retro-style bulb with state-of-the-art technology combined with vintage design.

Designed for the comfort of your eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

Looks good on and off



"These beautiful lamp with visible filament add a sense of styleand nostalgia to any room. Looks good on and off."

Specifications

Bulb characteristics

· Intended use: Indoor

· Lamp shape: Non directional globe

Socket: E27Dimmable: YesBulb Finish: PinkBulb Material: Glass

Durability

• Number of switch cycles: 20,000

· Nominal lifetime: 15,000

Environmental

 Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Guarantee

· Warranty period: 2.5 years

Light characteristics

Color rendering index (CRI): 80Color temperature: 1800 K

Nominal luminous flux: 250 lmWarm-up time to 60% light: 0.5 s

· Color Code: 818 | CCT of 1800K

 Correlated Color Temperature (Nom): 1800 K

· Luminous Flux: 250 lm

 Stroboscopic effect visibility measure (SVM): 0.4

 Luminous Efficacy (rated) (Nom): 55.00 lm/W

Miscellaneous

EyeComfort: Yes

· LED Innovations: EyeComfort

• Extra Features: Dimmable, Decorative

Other characteristics

• EU RoHS compliant: Yes

Packaging information

EAN: 8719514269552EOC: 871951426955200

• Product title: LED classic 25W G93

E27 pink D 1PF/4

Power

· Power Factor (Fraction): 0.7

Power consumption

Power factor: 0.5
Voltage: 220-240 V
Wattage equivalent: 25 W
Power Consumption: 4.5 W

• Energy Consumption kWh/1000 h: 5

Product dimensions and weight

Overall height: 140 mmOverall length: 140 mmOverall width: 95 mm

Rated values

· Rated lifetime: 15,000

Technical specifications

Frequency: 50-60Diameter: 95 mm

• Dimmable: Only with specific

dimmers

 Flickering value (PstLM) - Flickering value as per EN 61000-3-3:1

· Line Frequency: 50 to 60

· Cap-Base: E27

• can it be used in closed luminaires:

Packaging dimensions and weight

• EAN/UPC - product: 8719514269552

Net weight: 0.06 kgGross weight: 0.11 kgHeight: 18.2 cmLength: 10.2 cm

· Width: 13 cm



Issue date: 2025-09-13 Version: 0.257 © 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips