

# PHILIPS

Downlight

Recessed Lights

6500K

White

8719514303492



## High quality LED light designed to last for years

Light up your space with Philips EyeComfort LED Downlight that provides a comfortable light source and ease to your eyes.

### Easy to experience

- Ideal for rooms with low ceilings, makes for an unobtrusive and subtle fixture.

### Light effect

- Uniform light distribution

### Durability

- Long life span up to 15,000 hours

# Highlights

## Suitable for low ceilings Slim design Uniform light distribution

Throw light across your rooms in an even and uniform manner.

## Long life span up to 15,000 hours

Philips LED technology extends your product's lifetime up to 15,000 hours.

# Specifications

## Bulb characteristics

- Intended use: Indoor
- Lamp shape: Round

## Design and finishing

- Color: White
- Material: Plastic

## Durability

- Average life (at 2.7 hrs/day): 15 year(s)
- Lumen maintenance factor: 70%
- Number of switch cycles: 7,500

## Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

## Extra feature/accessory incl.

- Adjustable spot head: No
- Dimmable with remote control: No
- LED integrated: Yes
- Remote control included: No

## Light characteristics

- Beam angle: 100 degree(s)
- Color consistency: 6 SDCM
- Color rendering index (CRI): 80
- Warm-up time to 60% light: <2

## Miscellaneous

- Especially designed for: Bedroom, Living Room, Dining Room, Kitchen, Home Office
- Style: Contemporary
- Type: Recessed Lights
- EyeComfort: Yes

## Other characteristics

- Lamp current: 165 mA
- Efficacy: 82 lm/W

## Power consumption

- Power factor: 0.5

## Product dimensions and weight

- Net weight: 0.154 kg
- Cut out length: 20.0 cm
- Cut out width: 20.0 cm
- Height: 3.5 cm
- Length: 22.5 cm
- Recessed distance: 11.7 cm
- Width: 22.5 cm

## Service

- Warranty: 1 year(s)

## Technical specifications

- Lifetime up to: 15,000 hour(s)
- Diameter: 225 mm
- Total lumen output fixture: 1900
- Light color: 6500
- Mains power: AC 220-240
- Fixture dimmable: No
- LED: No
- Wattage bulb included: 23
- IP code: IP20
- Class of protection: Class II



Issue date: 2024-09-17  
Version: 0.162

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)