

# PHILIPS

Filament Bulb Smoky  
20W A160 E27

LED

1800K

200lm

15000h

Dimming



8719514315372



## State-of-the-art LED for the home

This Philips LED light bulb provides a beautiful, extra warm light, an exceptionally long life, and immediate, significant energy savings. With its flame color temperature, this light bulb is the perfect choice for a cozy atmosphere.

### **Dimmable extra warm white light**


- Dimmable extra warm white light

### **Designed to be seen, looks good on and off**

- Looks good on and off

# Highlights

## Dimmable extra warm white light



Offering cozy and warm ambiance in your room with extra warm white lights, which can dim to create your private atmosphere.

## Looks good on and off



"These beautiful lamp with visible filament add a sense of style and nostalgia to any room. Looks good on and off."

# Specifications

## Bulb characteristics

- Intended use: Indoor
- Lamp shape: Non directional bulb
- Socket: E27
- Dimmable: Yes
- Bulb Finish: smoky
- Bulb Material: Glass

## Durability

- Number of switch cycles: 20,000
- Ambient temperature range: -20 to +45 °C
- Nominal lifetime: 15,000

## Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

## Guarantee

- Warranty period: 2.5 years

## Light characteristics

- Color rendering index (CRI): 80
- Color temperature: 1800 K
- Nominal luminous flux: 200 lm
- Warm-up time to 60% light: 0.5 s
- Color Code: 818 | CCT of 1800K
- Correlated Color Temperature (Nom): 1800 K
- Luminous Flux: 200 lm
- Stroboscopic effect visibility measure (SVM): 0.4
- Luminous Efficacy (rated) (Nom): 30 lm/W

## Miscellaneous

- EyeComfort: Yes
- LED Innovations: EyeComfort
- Extra Features: Dimmable, Decorative

## Other characteristics

- CE mark: Yes
- EU RoHS compliant: Yes

## Packaging information

- EAN: 8719514315372
- EOC: 871951431537200
- Product title: LED giant 20W E27 A160 1800K smoky D

## Power

- Power Factor (Fraction): 0.7

#### Power consumption

- Power factor: 0.7
- Voltage: 220–240 V
- Wattage equivalent: 20 W
- Power Consumption: 6.5 W
- Energy Consumption kWh/1000 h: 7

#### Product dimensions and weight

- Overall height: 293 mm
- Overall length: 293 mm
- Overall width: 162 mm

#### Rated values

- Rated lifetime: 15,000

#### Technical specifications

- Frequency: 50–60
- Diameter: 162 mm
- Dimmable: Only with specific dimmers
- Flickering value (PstLM) – Flickering value as per EN 61000-3-3: 1
- Line Frequency: 50 to 60
- Cap-Base: E27
- can it be used in closed luminaires: No

#### Packaging dimensions and weight

- EAN/UPC – product: 8719514315372
- Net weight: 0.23 kg
- Gross weight: 0.49 kg
- Height: 32 cm
- Length: 18.5 cm
- Width: 18.5 cm



Issue date: 2025-09-24  
Version: 0.370

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)