

PHILIPS

Filament Bulb Amber
25W G93 E27

LED

1800K

250lm

15000h

Dimming



8719514315471



State-of-the-art LED for the home

This Philips LED light bulb provides a beautiful, extra warm light, an exceptionally long life, and immediate, significant energy savings. With its flame color temperature, this light bulb is the perfect choice for a cozy atmosphere.

Dimmable extra warm white light

- Dimmable extra warm white light

Designed to be seen, looks good on and off

- Looks good on and off

Highlights

Dimmable extra warm white light



Offering cozy and warm ambiance in your room with extra warm white lights, which can dim to create your private atmosphere.

Looks good on and off



"These beautiful lamp with visible filament add a sense of style and nostalgia to any room. Looks good on and off."

Specifications

Bulb characteristics

- Intended use: Indoor
- Lamp shape: Non directional globe
- Socket: E27
- Dimmable: Yes
- Bulb Finish: Amber
- Bulb Material: Glass

Durability

- Number of switch cycles: 20,000
- Ambient temperature range: -20 to +45 °C
- Nominal lifetime: 15,000

Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Guarantee

- Warranty period: 2.5 years

Light characteristics

- Color rendering index (CRI): 80
- Color temperature: 1800 K
- Nominal luminous flux: 250 lm
- Warm-up time to 60% light: 0.5 s
- Color Code: 818 | CCT of 1800K
- Correlated Color Temperature (Nom): 1800 K
- Luminous Flux: 250 lm
- Stroboscopic effect visibility measure (SVM): 0.4
- Luminous Efficacy (rated) (Nom): 62 lm/W

Miscellaneous

- EyeComfort: Yes
- LED Innovations: EyeComfort
- Extra Features: Dimmable, Decorative

Other characteristics

- CE mark: Yes
- EU RoHS compliant: Yes

Packaging information

- EAN: 8719514315471
- EOC: 871951431547100
- Product title: LED classic 25W G93 E27 GOLD SP D SRT4

Power

- Power Factor (Fraction): 0.7

Power consumption

- Power factor: 0.7
- Voltage: 220–240 V
- Wattage equivalent: 25 W
- Power Consumption: 4 W
- Energy Consumption kWh/1000 h: 4

Product dimensions and weight

- Overall height: 143 mm
- Overall length: 143 mm
- Overall width: 96 mm

Rated values

- Rated lifetime: 15,000

Technical specifications

- Frequency: 50–60
- Diameter: 96 mm
- Dimmable: Only with specific dimmers
- Flickering value (PstLM) – Flickering value as per EN 61000-3-3: 1
- Line Frequency: 50 to 60
- Cap-Base: E27
- can it be used in closed luminaires: No

Packaging dimensions and weight

- EAN/UPC – product: 8719514315471
- Net weight: 0.06 kg
- Gross weight: 0.11 kg
- Height: 18.2 cm
- Length: 10.2 cm
- Width: 13 cm



Issue date: 2025-09-13
Version: 0.409

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com