

Filament Bulb Amber 25W T32 E27

LED

1800K

250lm

15000h

Dimming



8719514315495



# State-of-the-art LED for the home

This Philips LED light bulb provides a beautiful, extra warm light, an exceptionally long life, and immediate, significant energy savings. With its flame color temperature, this light bulb is the perfect choice for a cozy atmosphere.

# Dimmable extra warm white light


• Dimmable extra warm white light

# Designed to be seen, looks good on and off

· Looks good on and off

# Highlights

#### Dimmable extra warm white light



Offering cozy and warm ambiance in your room with extra warm white lights, which can dim to create your private atomosphere.

# Looks good on and off



"These beautiful lamp with visible filament add a sense of styleand nostalgia to any room. Looks good on and off."

# Specifications

#### **Bulb characteristics**

· Intended use: Indoor

· Lamp shape: Non directional luster

Socket: E27Dimmable: YesBulb Material: Glass

#### **Bulb dimensions**

Height: 13.7 cmWidth: 3.3 cm

#### **Durability**

• Number of switch cycles: 20,000

Nominal lifetime: 15,000

#### **Environmental**

• Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

#### **Light characteristics**

· Color rendering index (CRI): 80

· Color temperature: 1800 K

· Nominal luminous flux: 250 lm

Warm-up time to 60% light: instant

ull light

· Color Code: 818 | CCT of 1800K

# Miscellaneous

EyeComfort: Yes

LED Innovations: EyeComfort

• Extra Features: Dimmable, Decorative

#### Other characteristics

· Efficacy: 62 lm/W

#### **Packaging information**

• EAN: 8719514315495

• EOC: 871951431549500

 Product title: LED classic 25W T32 E27 GOLD SP D SRT4

#### **Power consumption**

Power factor: 0.7Voltage: 220-240 VWattage: 4 W

· Wattage equivalent: 25 W

### Product dimensions and weight

• Length: 13.7 cm

**Technical specifications** 

• Frequency: 50-60 Hz



Issue date: 2025-05-13 Version: 0.299