



8719514337831



State-of-the-art LED light bulb for the home

This Philips LED light bulb provides a beautiful, extra warm light, an exceptionally long life, and immediate, significant energy savings. With its flame color temperature, this light bulb is the perfect choice for a cozy atmosphere.

Dimmable extra warm white light


• Dimmable extra warm white light

Designed to be seen, looks good on and off

· Looks good on and off

Highlights

Dimmable extra warm white light



Offering cozy and warm ambiance in your room with extra warm white lights, which can dim to create your private atomosphere.

Looks good on and off



"These beautiful lamp with visible filament add a sense of styleand nostalgia to any room. Looks good on and off."

Specifications

Bulb characteristics

· Intended use: Indoor

· Lamp shape: Non directional globe

Socket: E27Dimmable: YesBulb Material: Glass

Durability

• Number of switch cycles: 20,000

· Nominal lifetime: 15,000

Environmental

 Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Light characteristics

· Color rendering index (CRI): 80

· Color temperature: 2200 K

· Nominal luminous flux: 640 lm

• Warm-up time to 60% light: 0.5

· Color Code: 822 | CCT of 2200K

 Luminous Efficacy (rated) (Nom): 87 lm/W

Miscellaneous

EveComfort: Yes

· LED Innovations: EyeComfort

• Extra Features: Dimmable, Decorative

Packaging information

• EAN: 8719514337831

• EOC: 871951433783100

 Product title: LEDCLA 50W G120 E27 922 GOLD SP 1PF/4

Power consumption

• Power factor: 0.5

· Voltage: 220-240 V

· Wattage equivalent: 50 W

· Energy Efficiency Label (EEL): F

• Power Consumption: 7.3 W

• Energy Consumption kWh/1000 h: 8

Product dimensions and weight

· Overall height: 178 mm

• Overall length: 178 mm

· Overall width: 125 mm

Technical specifications

• Frequency: 50-60

• EPREL Registration Number: 574381

Packaging dimensions and weight

• EAN/UPC - product: 8719514337831

Net weight: 0.1 kgGross weight: 0.2 kg

Height: 22.6 cmLength: 13 cmWidth: 13 cm



Issue date: 2025-08-30 Version: 0.322 © 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips