

PHILIPS

Spot 50W PAR16
GU10

UltraEfficient

3000K

375lm

50000h



8720169174306



A light bulb like no other

Philips LED spots provide a focused bright beam, an exceptionally long life, and significant energy savings. This spot is the perfect long-lasting replacement for 50W spots with a GU10 cap.

Choose a simple replacement for your old bulbs

- Similar shape and size as standard halogen bulb

Choose for a sustainable solution

- Long life bulb - Lasts up to 50 years

High quality LED light that lasts for decades

- Designed for the comfort of your eyes

Highlights

Similar shape and size as standard halogen bulb



With its beautifully shaped design and familiar dimensions, this is a modern lighting energy-saving, standard, LED bulb. The perfect sustainable replacement for traditional standard halogen bulbs.

Long life bulb - Lasts up to 50 years



With a lifetime of up to 50,000 hours, you can reduce the hassle of frequently replacing your light bulbs, and enjoy a perfect lighting solution for over 50 years.

Designed for the comfort of your eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

Specifications

Bulb characteristics

- Intended use: Indoor
- Lamp shape: Directional reflector
- Socket: GU10
- Bulb Finish: Clear
- Dimmable: No
- Bulb Material: Glass

Durability

- Number of switch cycles: 50,000
- Nominal lifetime: 50,000

Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Light characteristics

- Beam angle: 36 degree(s)
- Color rendering index (CRI): 80
- Color temperature: 3000 K
- Nominal luminous flux: 375 lm
- Warm-up time to 60% light: 0.5
- Color Code: 830 | CCT of 3000K
- Luminous Efficacy (rated) (Nom): 178 lm/W

Miscellaneous

- EyeComfort: Yes
- LED Innovations: UltraEfficient, EyeComfort

Packaging information

- EAN: 8720169174306
- EOC: 872016917430600
- Product title: LEDClassic 50W GU10 WH 36D ND UE SRT4

Power consumption

- Power factor: 0.4
- Voltage: AC 220-240 V
- Wattage equivalent: 50 W
- Energy Efficiency Label (EEL): A
- Power Consumption: 2.1 W
- Energy Consumption kWh/1000 h: 3

Product dimensions and weight

- Overall height: 54 mm
- Overall length: 54 mm
- Overall width: 50 mm

Rated values

- Rated peak intensity: 680 cd

Technical specifications

- Frequency: 50-60
- EPREL Registration Number: 1428240

Packaging dimensions and weight

- EAN/UPC – product: 8720169174306
- Net weight: 0.05 kg
- Gross weight: 0.12 kg
- Height: 13.2 cm
- Length: 5.3 cm
- Width: 6.3 cm



Issue date: 2025-08-30
Version: 0.461

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com