

8720169187535



UltraEfficient lamp, our most energy efficient LED bulbs

Philips UltraEfficient LED lamps provide beautiful light, offer an exceptionally long lifetime of 50,000 hours, and deliver immediate and significant energy savings. Reduce the frequency of lamp replacements and enjoy light that's easy on the eyes with our trusted EyeComfort design.

High quality light

• Designed for the comfort of your eyes

Designed to last longer and save more energy

- · Everyday switch on, save energy
- · Long life bulb Lasts up to 50 years

Highlights

Designed for the comfort of your eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get the glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

Everyday switch on, save energy



Our UltraEfficient LEDs are at least 50% more energy-efficient than standard Philips LEDs, saving you energy every day

Long life bulb - Lasts up to 50 years



Avoid the hassle of frequent light bulb replacements. With a lifetime of up to 50,000 hours, our UltraEfficient LEDs last 3.5 times longer than standard Philips LEDs, so you can enjoy a perfect lighting solution for more than 50 years.

Specifications

Bulb characteristics

· Intended use: Indoor

· Lamp shape: Non directional bulb

· Socket: E27

Bulb Finish: FrostedDimmable: No

· Bulb Material: Glass

Durability

• Number of switch cycles: 500,000

· Nominal lifetime: 50,000

Environmental

• Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Light characteristics

• Beam angle: 300 degree(s)

· Color rendering index (CRI): 80

· Color temperature: 2700 K

· Nominal luminous flux: 485 lm

• Warm-up time to 60% light: instant

full light

· Color Code: 827 | CCT of 2700K

Luminous Efficacy (rated) (Nom): 210 lm/W

Miscellaneous

EyeComfort: Yes

 LED Innovations: EyeComfort, UltraEfficient

Packaging information

. EAN: 8720169187535

• EOC: 872016918753500

 Product title: LED CLA 40W A60 E27 2700K FR UE SRT4

Power consumption

• Power factor: 0.4

Voltage: AC 220-240 V

· Wattage equivalent: 40 W

• Energy Efficiency Label (EEL): A

• Power Consumption: 2.3 W

• Energy Consumption kWh/1000 h: 3

Packaging dimensions and weight

• EAN/UPC - product: 8720169187535

Net weight: 0.03 kgGross weight: 0.05 kg

Height: 14.6 cmLength: 6.5 cm

· Width: 6.3 cm

Product dimensions and weight

Overall height: 104 mmOverall length: 104 mmOverall width: 60 mm

Technical specifications

• Frequency: 50-60

No

EPREL Registration Number: 1442603can it be used in closed luminaires:



Issue date: 2025-09-13 Version: 0.509 © 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips