

8720169263895



Our most energyefficient LED lights yet

Give your outdoor wall a heritage look, with the black Philips LED outdoor wall light. Its diffused, bright light is also ideal for lighting up your front entrance. Its retro design is a stylish way to enjoy your outdoor moments.

Easy installation

No wiring requried

Sustainable light solutions

- · Long lifetime up to 50,000 hours
- · Ultra Efficient Solar

Designed for outdoors

• IP44 - weather proof

Special characteristics

- Dual-brightness light
- Motion and Dusk-to-dawn sensor integrated

High quality light

· Bright white light 3000K

Highlights

No wiring requried



This light is powered entirely by solar energy. No wiring is needed, making these lights easy to position and reposition anywhere in your garden or other outdoor area.

Long lifetime up to 50,000 hours



Reliable high-quality LED light lasts up to 50,000 hours. You can rest easy knowing that you won't have to worry about maintenance for years, while enjoying the perfect garden light every night.

Ultra Efficient Solar



With the Philips Ultra Efficient Solar system, these luminaires provide light for up to 35 hours on a fully-charged battery. Enjoy bright light all night, or even in bad or overcast weather conditions.

IP44 - weather proof



This Philips outdoor light is especially designed for humid outdoor environments and has been tested rigorously to ensure water resistance. Its IP44 rating means that it has been certified to offer ingress protection against dust and splashing water—perfect for general outdoor use.

Dual-brightness light

Create a flexible and appealing ambiance with the dual-brightness feature. The light dims when idle and automatically brightens when people are present, delivering the right level of light whenever you need it.

Motion and Dusk-to-dawn sensor integrated



With a built-in motion sensor, these lights automatically welcome you when you return home after dark, or light up when visitors arrive. The unique dusk-to-dawn feature turns the lights on automatically when it gets dark outside--perfect for those long summer evenings or to ensure your safety.

Bright white light 3000K



Did you know that different shades of white light are identified by different color temperatures, measured in Kelvin (K)? Lower color temperatures produce a warm, cozy white light, while higher color temperatures produce a cool, more energizing white light. This luminaire produces bright white light at 3000 K.

Specifications

Design and finishing

Color: BlackMaterial: Plastic

Durability

· Nominal lifetime: 50,000

Environmental

• Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- · Adjustable spot head: Not adjustable
- · Anti rust anti dust: Yes
- · Bi-directional light beams: No
- · Day-and-night sensor: Yes
- Fully weatherproof: Yes
- · LED integrated: Yes
- Motion sensor: Yes
- · Solar Energy: Yes
- Warm White Light: No
- · Centerpiece: No

Garden area

· Garden area: Garden & Patio

Light characteristics

- · Color rendering index (CRI): 80
- · Color temperature: 3000 K

Miscellaneous

- Especially designed for: Garden, Patio
- Style: ContemporaryType: Wall Lights
- EyeComfort: NoLED Innovations: UltraEfficient
- Extra Features: Sensor, Solar, Water Resistant

Product dimensions and weight

- · Net weight: 0.48 kg
- Overall height: 205 mm
- · Overall length: 190 mm
- · Overall width: 140 mm

Service

· Warranty: 5 year(s)

Technical specifications

- · Total lumen output fixture: 250
- · Light color: 3000K
- · Mains power: 4 V
- Fixture dimmable: No
- Energy class included light source: A
- Maximum wattage replacement bulb:
 14
- IP code: IP44 | Wire-protected and splash-proof
- Class of protection: Class III Safe Extra Low Voltage
- · Light source replaceable: Yes

Packaging dimensions and weight

- EAN/UPC product: 8720169263895
- Net weight: 0.48 kgGross weight: 0.7 kg
- Height: 24 cmLength: 16.5 cm
- Width: 15 cm



Issue date: 2025-09-17 Version: 0.354

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.