

Radii Wall Light 1.3W

Outdoor luminaires

3000K

Black

Linkable;Sensor;Solar;Water Resistant



8720169267176





Our most energyefficient LED lights yet

Philips has developed an UltraEfficient solar LED outdoor light that uses new technology to cut carbon emissions, reduce material waste, and lower energy usage. With an amazing 50,000 hour lifetime it lasts more than 5 times longer than the Philips LED outdoor light equivalents. Just what is needed for a more sustainable planet.

Easy installation

· No wiring requried

Sustainable light solutions

· Ultra Efficient Solar

Bring design into your garden

· Choose for outdoor wall lights

Advanced LED light

• 5 year warranty on LED system

Designed for outdoors

• IP44 - weather proof

High quality light

· Bright white light 3000K

Highlights

No wiring requried



This light is powered entirely by solar energy. No wiring is needed, making these lights easy to position and reposition anywhere in your garden or other outdoor area.

Ultra Efficient Solar



With the Philips Ultra Efficient Solar system, these luminaires provide light for up to 40 hours on a fully-charged battery. Enjoy bright light all night, or even in bad or overcast weather conditions.

Choose for outdoor wall lights

Make the most of your outdoor space with this wall light, perfect to mount close to your front door or on your terrace walls.

5 year warranty on LED system



In addition to the standard 2-year warranty offered for this luminaire, Philips also offers a 5-year warranty on the LED system (the LED module and driver).

IP44 - weather proof



This Philips outdoor light is especially designed for humid outdoor environments and has been tested rigorously to ensure water resistance. Its IP44 rating means that it has been certified to offer ingress protection against dust and splashing water—perfect for general outdoor use.

Bright white light 3000K



Did you know that different shades of white light are identified by different color temperatures, measured in Kelvin (K)? Lower color temperatures produce a warm, cozy white light, while higher color temperatures produce a cool, more energizing white light. This luminaire produces bright white light at 3000 K.

Specifications

Design and finishing

Color: BlackMaterial: Plastic

Durability

· Nominal lifetime: 50,000

Environmental

 Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- · Adjustable spot head: Not adjustable
- · Anti rust anti dust: Yes
- · Bi-directional light beams: No
- · Day-and-night sensor: Yes
- Fully weatherproof: Yes
- · LED integrated: Yes
- Motion sensor: Yes
- · Solar Energy: Yes
- · Warm White Light: No
- · Centerpiece: No

Garden area

· Garden area: Garden & Patio

Light characteristics

- · Color rendering index (CRI): 80
- · Color temperature: 3000 K

Miscellaneous

- Especially designed for: Garden, Patio
- Style: ContemporaryType: Wall Lights
- EyeComfort: No
- LED Innovations: UltraEfficientExtra Features: Linkable, Sensor,
 - Solar. Water Resistant

Product dimensions and weight

- · Net weight: 0.74 kg
- · Overall height: 192 mm
- · Overall length: 240 mm
- Overall width: 175 mm

Service

· Warranty: 5 year(s)

Technical specifications

- · Total lumen output fixture: 250
- · Light color: 3000K
- · Mains power: 4 V
- · Fixture dimmable: No
- · Energy class included light source: A
- Maximum wattage replacement bulb:
 13
- IP code: IP44 | Wire-protected and splash-proof
- Class of protection: Class III Safe Extra Low Voltage
- · Light source replaceable: Yes

Packaging dimensions and weight

- EAN/UPC product: 8720169267176
- Net weight: 0.74 kgGross weight: 1.13 kg
- Height: 27 cm
 Length: 20 cm
 Width: 20 cm



© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips



