



8720169296503



Light up your outdoor life

This Philips Alula solar portable light has 3 in 1 light setting modes. By simple knock or tap you can enjoy two brightness level or RGB party mode.

Sustainable light solutions

· Long lifetime up to 15,000 hours

Advanced LED light

· High quality LED light

Premium quality

· High quality material

Designed for outdoors

· IP44 - weather proof

Highlights

Long lifetime up to 15,000 hours



Reliable high-quality LED light lasts up to 15,000 hours. You can rest easy knowing that you won't have to worry about maintenance for years, while having the perfect light ambiance in your home.

High quality LED light



These LED lights use a unique technology developed by Philips. They turn on instantly and produce optimal light output that brings out the vivid colors in your garden.

Specifications

Design and finishing

Color: BlackMaterial: Plastic

Durability

• Nominal lifetime: 15,000

High quality material



This Philips outdoor lamp is made of high quality materials with superior finishing. This ensures a solid and long lasting product which is resistant to corrosion and stains in all weather conditions

IP44 - weather proof



This Philips outdoor light is especially designed for humid outdoor environments and has been tested rigorously to ensure water resistance. Its IP44 rating means that it has been certified to offer ingress protection against dust and splashing water—perfect for general outdoor use.

Environmental

• Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- · Adjustable spot head: Not adjustable
- · Anti rust anti dust: Yes
- · Bi-directional light beams: No
- Day-and-night sensor: No
- · Fully weatherproof: Yes
- · LED integrated: Yes
- · Motion sensor: No
- · Solar Energy: Yes
- Centerpiece: Yes

Light characteristics

- Beam angle: 120 degree(s)
- · Color rendering index (CRI): 80
- · Color temperature: 3000 K

Miscellaneous

- Especially designed for: Garden, Patio
- Style: Contemporary
- Type: Portable Lights
- EyeComfort: No
- Extra Features: RGB Colors, Solar, Water Resistant

Power consumption

• Power Consumption: 1.2

Product dimensions and weight

Net weight: 0.362 kgOverall height: 150 mmOverall length: 130 mm

· Overall width: 120 mm

Service

• Warranty: 1 year(s)

Technical specifications

- Total lumen output fixture: 80/20
- Light color: 3000Mains power: 5, DC 4
- Fixture dimmable: No
- Energy class included light source: FIP code: IP44 | Wire-protected and
- splash-proof
- · Class of protection: Class III Safe
- Extra Low Voltage
- · Light source replaceable: No

Packaging dimensions and weight

- EAN/UPC product: 8720169296503
- Net weight: 0.36 kgGross weight: 0.44 kg
- Height: 12 cmLength: 14 cmWidth: 15 cm



Issue date: 2025-10-03 Version: 0.172 © 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips