

PHILIPS

Sparkle Recessed
light

Recessed Lights

2700K

Black

Dimmable



8720169304215



Comfortable LED light that's easy on your eyes

Create the perfect mood with Philips LED Dimmable recessed spots, you can easily dim your lights from everyday bright light to cosy tones

Sustainable light solutions

- High quality LED light

Light effect

- Bright and focused beam

Control

- Dimmable

Durability

- Long life span up to 20,000 hours

Highlights

High quality LED light



The LED technology, integrated into this Philips lamp, is a uniquely developed solution by Philips. While instantly turned on, it enables an optimal light output and brings out vivid colors in your home.

Bright and focused beam

Focus light on objects, a dining table or other interiors to draw attention to particular stylings.

Dimmable

Allows you to change the mood by reducing LED brightness levels, from bright white light, to a cozy glow – just like traditional lamps.

Long life span up to 20,000 hours

Philips LED technology extends your product's lifetime up to 20,000 hours.

Specifications

Bulb characteristics

- Intended use: Indoor

Design and finishing

- Color: Black
- Material: Metal, Plastic

Durability

- Number of switch cycles: 10,000
- Nominal lifetime: 20,000

Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- Adjustable spot head: Adjustable – rise and fall
- Dimmable with remote control: No
- LED integrated: Yes
- Remote control included: No

Light characteristics

- Beam angle: 36 degree(s)
- Color consistency: 6 SDCM
- Color rendering index (CRI): 80
- Color temperature: 2700 K
- Warm-up time to 60% light: 2
- Luminous Efficacy (rated) (Nom): 64 lm/W

Miscellaneous

- Especially designed for: Bedroom, Dining Room, Garage, Hall, Office, Kitchen, Living Room
- Style: Modern
- Type: Recessed Lights
- EyeComfort: Yes
- LED Innovations: EyeComfort
- Extra Features: Dimmable

Other characteristics

- Lamp current: 29 mA

Power consumption

- Power factor: 0.8
- Power Consumption: 5

Product dimensions and weight

- Net weight: 0.118 kg
- Recessed distance: 20 mm
- Overall height: 60 mm
- Recessed Ceiling cutout: 7.0 cm x 7.0 cm

Service

- Warranty: 2 year(s)

Technical specifications

- Diameter: 85 mm
- Total lumen output fixture: 350
- Light color: 2700
- Mains power: AC 220-240
- Fixture dimmable: Yes
- IP code: IP20 | Finger-protected
- Class of protection: Class II – Double Insulated
- Number of light sources: 1



Issue date: 2025-09-03
Version: 0.204

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com