

# PHILIPS

Filament Bulb Amber  
25W ST64 E27

LED

1800K

270lm

15000h

Dimming



8721103049056



## Decorate your home with natural light

Both decorative and functional, this light bulb has an elegant, vintage design with a visible spiral filament and provides bright, natural light with excellent color rendering. Start saving energy right away with a bulb that will last for 15,000 hours.

### High quality light

- Designed for the comfort of your eyes

### High quality LED light that lasts for decades

- Light that shows true colors

### Designed to be seen, looks good on and off

- Classic glass LED

### Vintage bulb design with spiral filament

- This is a light designed for beauty and performance, with a vintage design and a visible spiral filament. Bring a touch of style and elegance to any room, whether the light is switched on or off.

### High-performance spiral slim filament

- The delicate spiral filament adds to the bulb's aesthetic appeal. Create a warm and welcoming atmosphere with soft and natural light that offers excellent color rendering at CRI 90.

# Highlights

## Designed for the comfort of your eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get the glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go

easy on the eyes, and create the perfect ambience for your home.

## Light that shows true colors



See the true colors of your clothes when you select an outfit from your wardrobe – you can pair a red dress and red shoes with confidence and be sure the colors match perfectly.

## Glass Clear Design

The look you love, the performance you expect. Classic clear glass designs that replicate the beautiful sparkling light of traditional bulbs, for a perfect fit throughout your home.

## Vintage bulb design

## High-performance slim filament

# Specifications

## Bulb characteristics

- Intended use: Indoor
- Lamp shape: Non directional bulb
- Socket: E27
- Bulb Finish: Amber
- Dimmable: Yes
- Bulb Material: Glass

## Durability

- Number of switch cycles: 20,000
- Nominal lifetime: 15,000

## Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

## Light characteristics

- Beam angle: 300 degree(s)
- Color rendering index (CRI): 90
- Color temperature: 1800 K
- Nominal luminous flux: 270 lm
- Luminous Efficacy (rated) (Nom): 87 lm/W

## Miscellaneous

- EyeComfort: Yes
- LED Innovations: EyeComfort
- Extra Features: Decorative, Dimmable

## Packaging information

- EAN: 8721103049056
- EOC: 872110304905600
- Product title: LED ST64 25W 1800K E27 Amber SP D 1PF/4

## Power consumption

- Power factor: 0.5
- Voltage: AC 220-240 V
- Wattage equivalent: 25 W
- Power Consumption: 3.1 W
- Energy Consumption kWh/1000 h: 4

#### Product dimensions and weight

- Overall height: 139 mm
- Overall length: 139 mm
- Overall width: 64 mm

#### Technical specifications

- Frequency: 50-60
- can it be used in closed luminaires:  
No

#### Packaging dimensions and weight

- EAN/UPC - product: 8721103049056
- Net weight: 0.05 kg
- Gross weight: 0.07 kg
- Height: 17.7 cm
- Length: 7.5 cm
- Width: 7.6 cm



Issue date: 2025-10-04  
Version: 0.226

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)