

Project		Catalog #		Type	
Prepared by		Notes		Date	



HALO

3003 Series

3-Inch Adjustable Baffle Trim

For use with Halo small aperture line and low voltage housings.

Product Specifications


Cast aluminum trim ring with machined Coilex® baffle available in Matte White, Black, or Tuscan Bronze finishes. Three pressure springs ensure positive retention in housing.

Trim includes cover glass lens which may be replaced with a variety of media. (Lamps that have integral glass lens do not require use of the cover glass supplied with this trim.)

3003 is designed for use with the following HALO H3 small aperture housings:

- Line Voltage Housing (for 120V GU10 lamps)
 - H36ICAT 50W IC Air-Tite Housing
 - H36TAT 50W Non-IC Air-Tite Housing
 - H36RTAT 50W Non-IC Air-Tite Remodel Housing
- Low Voltage Housing (for 12V MR16 lamps)
 - H36LVICAT 50W IC Air-Tite Housing
 - H36LVTAT 50W Non-IC Air-Tite Housing
 - H36LVRTAT 50W Non-IC Air-Tite Remodel Housing
 - H36LVTAT277 50W Non-IC Air-Tite Housing, 120/277V
 - H36LVRTAT277 50W Non-IC Air-Tite Remodel Housing, 120/277V
- Line Voltage Housing (for 120V GU10 lamps)
 - H38ICAT 50W IC Air-Tite Housing
- Low Voltage Housing (for 12V MR16 lamps)
 - H38LVICAT 50W IC Air-Tite Housing

Dimensional Details



- Lamp Aperture: 2" [51mm]
- Baffle Diameter: 3" [75mm]
- Ceiling Opening: 3-3/4" [95mm]
- Outside Diameter: 4-1/4" [108mm]

Order Information

SAMPLE ORDER NUMBER: **3003WHBB**

Module	Finish
3003-3" Adjustable Baffle Trim	BKBB =Black with Black Baffle TBZB =Tuscan Bronze with Tuscan Bronze Baffle WHBB =White with Black Baffle WHWB =White with White Baffle



3003BKBB
Black Coilex Baffle and Trim



3003TBZB
Tuscan Bronze Coilex Baffle and Trim



3003WHBB
Black Coilex Baffle with White Trim



3003WHWB
White Coilex Baffle and Trim