



Project: \_\_\_\_\_

Location: \_\_\_\_\_

Cat.No: \_\_\_\_\_

Type: \_\_\_\_\_

Lamps: \_\_\_\_\_ Qty: \_\_\_\_\_

Notes: \_\_\_\_\_

Complete fixture consists of Reflector Trim & Frame-in Kit. Select each separately

Reflector Trim		Frame-in Kit (Incandescent)		Lamp	Voltage
516WHX	White	Remodeler Non-IC	501X	50W PAR20	120V
		Frame Non-IC	502X	50W PAR20	120V
		Lytening Frame AirSeal®	502AICSX	50W PAR20	120V

#### Features

**Housing** : 25ga galvanized steel.

**Residence Mounting Clips**: Factory-installed; zinc plated spring steel; free-hand installation.

**Face Plate**: 23ga. Cold roll steel. One piece face plate/ lamp housing (non-adjustable). Gasket included for shower applications (white finish). May be removed if not required.

**Mounting Clips (2)**: 28ga. Stainless steel spring.

#### Accessories

500SQBK Black Square Plate  
500SQWH White Square Plate

#### Marking

cCSAus Certified, suitable for damp and wet locations

#### Frame-in Kit

See Frame-In Kit specification sheets for more details. appropriées.

