DESCRIPTION

The 160 series is a decorative wall sconce family with half cylindrical form. This product is a half circular column shape shade, with a variety of options to highlight elegant spatial forms. The integral LED light engine is available in 2700K, 3000K, 3500K, and 4000K color temperatures that evenly illuminates the shade and the bottom lens, and 83+ CRI. Shaper's Fabrique collection its known for is high quality hand tucked fabrics. Heavy gauged steel frame, laminated styrene backing, and minimum internal structure. Shades come in three standard sizes, eleven standard fabrics, three vinyl materials (25" and 37" only), four printed wood patterns (25" and 37" only), and two translucent organza fabrics, allowing the designer to select a look for any space.

Shaper

Catalog #	Туре
Project	
Comments	Date
Prepared by	

SPECIFICATION FEATURES

Construction

Aluminum housing, cold rolled steel cover and bracket extensions with LED boards attached. Optional matte white acrylic top cover available (TC).

<u>160-25</u> Standard length = 25" OAH (Overall Height)

<u>160-37</u> Standard length = 37" OAH (Overall Height)

<u>160-49</u> Standard length = 49" OAH (Overall Height)

Shades

Aluminum wire frame painted white. Material backed on to heavy translucent white styrene. All shades have "Hand-Tucked Rolled Edges" except for Vinyl.

Fabric Shade Selections SIW - Silk White SIY - Silk Ivory SWH - Shantung White

SWH - Shantung White SEG - Shantung Eggshell SBG - Shantung Beige GBB - Glynn Brussels Beige LOLA - Lola Sand NGS - Silk Glow LCK - Linen Chopstick LAT - Linen Alabaster VLW - Verona Linen White <u>Vinyl Coated Fabric</u> ABR - Alabaster Vinyl NFX - Natural Flax GHY - Golden Honey Note: not available for 49."

Printed Wood

PVDB - Varigated Bamboo PVDB - Varigated Bamboo PMA - Maple PCH - Cherry PWA - Walnut **Note:** For humid environments, such as showers or open lobbies, Vinyl Coated Fabrics are recommended. Not available for 49". <u>Organza Outer Shade Options</u> EDT - Earth Dust WMT - White Mist

LEDs

LEDs are offered in four color temperatures: 2700K, 3000K, 3500K, and 4000K CCTs at 80+ CRI. Rated Lamp Life: 50,000 hrs

Electrical

Standard driver is electronic universal voltage (120-277V, 50/60 Hz), greater than 0.9 power factor, less than 20% harmonic distortion, and ambient temperatures of 25°C (77°F).

Control

Standard driver is 0-10V with 10% dimming.

Compliance

Components are UL recognized and luminaires are cUL listed for 25° ambient environments. Fixtures are rated for damp location listing. Made in North America. Cooper Lighting Solutions certifies that its products satisfy the requirements of ARRA Section 1605 of the American Recovery Reinvestment Act. All LED components are RoHS compliant and drivers conform to appropriate FCC regulations. Sconce products meet ADA regulations.

Life and Warranty

Standard five-year warranty on all parts.



160-W Series

Surface

Decorative LED Wall Sconce

cULus – 1598 Damp Location LM79/LM80 Compliant

Length 25"

- Delivered Lumens (@3500K) 1935
- Wattage: 22W
- CRI: 80 • CCT: 2700K, 3000K, 3500K, 4000K

Length 49"

- Delivered Lumens (@3500K) 3797
- •Wattage: 41W
- CRI: 80 • CCT: 2700K, 3000K, 3500K, 4000K

Length 49-SIW"

- Delivered Lumens (@3500K) 2158
 Wattage: 41W
- CRI: 80
- CCT: 2700K, 3000K, 3500K, 4000K

ORDERING INFORMATION (Select FIXTURE NUMBER and SHADE NUMBER to complete specification)

Fixture Number: 160-25-W-L3/827-UNV

Series 1	Size	Mounting Type	LED Lamp			LED Voltage	Options ²
160 = Round Cylinder Wall Sconce	25″ 37″ 49″	W = Wall	25" L3/827 L3/830 L3/835 L3/840	37" L4/827 L4/830 L4/835 L4/840	49" L5/827 L5/830 L5/835 L5/840	UNV (120-277)	TC = Matte White Acrylic Top Cover RBP = Remote Battery Pack

Notes: ¹ Fabric Kit is not included. Please specify Fabric Kit (below) to complete specification. ² 5'Max Mounting Distance.

Shade Number: 160-25-SHD-SIW

Series	Size	Shade	Finish			Options
160 = Round Cylinder Shade	25″ 37″ 49″	SHD = Shade Fabric	Fabric: 12.3 SIW = Silk White SIY = Silk Ivory SWH = Shantung White SEG = Shantung Eggshell SBG = Shantung Beige GBB = Glynn Brussels Beige	LOLA = Lola Sand NGS = Silk Glow LCK = Linen Chopstick LAT = Linen Alabaster VLW = Verona Linen White	Vinyl: ¹² ABR = Alabaster Vinyl NFX = Natural Flax GHY = Golden Honey Printed Woods: ¹² PVDB = Varigated Bamboo PMA = Maple PCH = Cherry PWA = Walnut	Organize Shade in Shade WRDSIS-EDT = Earth Dust WRDSIS-WMT = White Mist

Notes: 1 Available for 25", 2 Available for 37", 3 Available for 49"





