

## DESCRIPTION

A low brightness 4-1/2 inch aperture adjustable accent fixture for PAR30, PAR20 and PAR16 LED lamps (20W max). Optics allow the lamp axis to pivot about the center of the aperture at the ceiling line, allowing maximum light output with no flashback. 20° truncated cone allows full range and flexibility of aiming.

Catalog #		Type
Project		
Comments		Date
Prepared by		

## SPECIFICATION FEATURES

### Reflector

Spun 0.040" aluminum. Available in a variety of Alzak® finishes. Painted white finish as well as white or black baffles. Torsion springs pull trim tight to ceiling. Reflector is keyed to prevent improper orientation relative to lamp. PAR20 and PAR16 lamps can be removed through the reflector.

### Trim Ring

Self flanged or white painted die cast trim ring.

### Aiming Mechanism

Stable lamp aiming and locking mechanism allows smooth 358° rotation and 35° elevation adjustment. Lamp aiming scale enables consistent setting across multiple fixtures.

### Housing

One piece die cast 1" deep collar. Housing is painted optical matte black to eliminate stray light.

### Universal Mounting Bracket

Accepts 1/2" EMT, C Channel, T bar fasteners and hanger bars. Provides 5" total adjustment.

### Junction Box

Listed for eight #12g (four in, four out) 90°C conductors feed through branch wiring. Pry-outs for six 1/2" conduits and 4 integral Romex traps. Access to junction box through panel in side of housing.

### Socket

Medium base porcelain socket with nickel plated screw shell.

### Insulation Detector

Self-resetting insulation detector opens circuit if insulation is improperly installed.

### Labels

cULus listed, damp location.



**H7443T**  
**9471/9473**

20W MAX


PAR30

PAR20

PAR16

4-1/2-Inch Adjustable

## DIMENSIONS



## ORDERING INFORMATION

Housing	Options	Max Wattage Label	Trims	Finish	Option	Accessories
<b>H7443T</b> =4" Directional, PAR lamp	<b>CP</b> =Chicago Plenum	<b>WL8</b> =8W <b>WL12</b> =12W <b>WL20</b> =20W	<b>9471</b> =Self Flanged <b>9473</b> =Metal Trim Ring	<b>B</b> =Specular Black <b>GPH</b> =Graphite Haze <b>H</b> =Semi-Specular Clear <b>LI</b> =Specular Clear <b>MW</b> =Matte White <b>WH</b> =Wheat <b>WMH</b> =Warm Haze <b>BB</b> =Black Baffle (9473 only) <b>WB</b> =White Baffle (9473 only)	<b>WF</b> =White Painted Flanged (Self Flanged only)	<b>H277</b> =Step Down Transformer, 300VA Max <b>HB26</b> =C Channel Bar Hangers, 26" Long, Pair <b>HB50</b> =C Channel Bar Hangers, 50" Long, Pair <b>FK5</b> =5 Amp Field Installable Fuse Kit 300V Max <b>RMB-22</b> =Wood Joist Bar Hanger, 22" Long, Pair <b>L200 Series</b> =Optical Lenses for PAR lamps, use with LC30 Lens Clips <b>LC30</b> =Lens Holder for PAR30 Lamps and L200 Series Lens