

Project: _____


Location: _____

Cat.No: _____

Type: _____

Lamps: _____ Qty: _____

Notes: _____



Ordering Guide

Example: BUL16 A S7 LED7 NF W

Product Code	BUL16	LED Composite Bullyte
Finish	A H G	Black Bronze Verde
Mounting	S7	Mounting Stake
Source/Lumens	LED7	7W LED
Optics	NF FL	Narrow Flood Flood
CCT	W	Warm

*1 Fixture will be shipped with lamp. Lamp not sold separately.

Specifications

HOUSING:

One-piece injection molded ULTEM® High Performance Polymer composite. Fully rotatable shroud, gasketed, ULTEM® High Performance Polymer composite. Fully-adjustable swivel arm with vibration-proof locking teeth. ½" NPS male threads to screw onto accessory mounting stake or junction box. Fasteners are 300 series stainless steel. Gasketing is silicone.

FINISH:

Composite is textured, pressure formed, molded-in-color.

OPTICAL ASSEMBLY:

Clear tempered glass affixed at 10° angle for natural cleaning.

LAMPING:

7W lamp with 25° or 35° beam spread, 25,000 hours life. Color temperature (CCT): Warm White (3,000K nominal). No Mercury. Dimmable. Approximately 460 lumens.

ELECTRICAL ASSEMBLY:

Bi-pin socket type (GU5.3) with 250° C high temperature teflon coated wire leads. Stainless steel retention clip affixed to socket to securely hold lamp in place. The wires are permanently fused to the clip. Stainless Steel lamp clip is designed to prevent arching of bi-pin and also acts as a heat sync to keep heat away from the socket. Electrical internal connectors are stainless steel 12 Volt fixture is pre-wired with 3-ft pigtail of 18-2 AWG, 105° C, SPT-1W wire. Low voltage quick connector, catalog #LVC3 included for easy hook-up to the low voltage supply cable, not included. 12 Volt system requires remote transformer, not included.

WARRANTY:

Five-year limited warranty.

CERTIFICATIONS:

ETL listed to U.S. safety standards for wet locations. cETL listed to Canadian safety standards for wet locations. Manufactured to ISO 9001:2008 Standards.

Width: 2 1/8" (80mm) **Length:** 6 1/2" (165mm) **Max. Weight:** 1.16 lb

