

# LUMEC

by @signify

Urban

Ancestra

AT10-20-30-40-50  
Post Top and Pendant



Built to perform, its' eye-catching design will set your project apart. The **Ancestra** luminaire presents a new twist on an old-fashioned design. By combining the most popular aspects of past and present forms with the best that modern technology has to offer, the Ancestra epitomizes Lumec's design philosophy beautifully: to combine superior technology with an elegant design.

Project: \_\_\_\_\_

Location: \_\_\_\_\_

Cat.No: \_\_\_\_\_

Type: \_\_\_\_\_

Lamps: \_\_\_\_\_ Qty: \_\_\_\_\_

Notes: \_\_\_\_\_

## Ordering guide sample

Luminaire	Lamp	Optical System	Voltage	Options	Mountings	Pole*	Finish**
AT10-SHA-PH	50MH	SHA	120	FN	CRA	RTA906/907	

\* Consult the eCatalog for details and the complete line of poles.


The specially formulated Luminal powder coat finish is available in a range of many standard colors.

\*\* Consult Lumec's Color Chart for complete specifications.

## Luminaires


Conform to the UL 1598 and CSA C22.2 No. 250.0-08 standards.

AT10-SHA-PH




**Weight:** 47 lbs (21.3 kg)  
**EPA:** 1.86 sq. ft

AT20-SCB3M-DA




**Weight:** 47 lbs (21.3 kg)  
**EPA:** 1.58 sq. ft

AT30-SHA-DC




**Weight:** 47 lbs (21.3 kg)  
**EPA:** 1.86 sq. ft

AT40-SCB3M




**Weight:** 47 lbs (21.3 kg)  
**EPA:** 1.58 sq. ft

AT50-SHA



**Weight:** 42 lbs (19.1 kg)  
**EPA:** 1.35 sq. ft

AT50-SHA-GRD-CR30



**Weight:** 58 lbs (26.3 kg)  
**EPA:** 1.58 sq. ft

# AT10-20-30-40-50 Ancestra

## Post Top and Pendant

### Lamp / HID

Wattage	SCB3M / SHA3M-PC / SSA3M-PC	SHA3M-ACDR / SSA3M-ACDR
50MH, medium	■	■
70MH, medium	■	■
100MH, medium	■	■
150MH, medium	■	■
200MH, mogul	■	N/A
175PSMH, mogul	■	■
250PSMH, mogul	■	N/A
35HPS, medium	■	■
50HPS, mogul	■	■
70HPS, mogul	■	■
100HPS, mogul	■	■
150HPS, mogul	■	■
200HPS, mogul	■	N/A
250HPS, mogul	■	N/A

■ Available. N/A : Not available.

### Optical System / HID

(Lamps not included)



**SHA and SSA optics**  
Sealed optical chamber consisting of a reflector permanently assembled on top of an internal prismatic globe.

**SHA3M** Asymmetrical

**SSA3M** Asymmetrical

> House shield available in option (HS)

In the above optics, the sleeve and shutter permit exact positioning of the lamp.  
**SHA & SSA** refractors available in: **ACDR**: Acrylique (175 W max.), **PC**: Polycarbonate.  
Add suffix to optical system code.



**SCB optics**  
Sealed optical chamber consisting of a reflector permanently assembled on top of a tempered-glass sag lens.

**SCB3M**: Asymmetrical

> House shield available in option (HS)

In the above optics, the sleeve and shutter permit exact positioning of the lamp.

### Voltage


HID <sup>1</sup>
120
208
240
277
347
480

1. Multi-top ballast also available.

### Options


- FN** Decorative finial (see on the right)
- FNC** Copper-color painted finial (except AT50)
- DA** Decorative arches
- DC** Decorative caps
- CPT** Copper cupola
- CPTC** Varnished copper cupola (except AT50)
- GRD** Decorative grid (AT50 only)
- CR20** Decorative crown (AT50 only)
- CR30** Decorative crown (AT50 only)
- CR40** Decorative crown (AT50 only)
- HS** House shield
- PH** Photoelectric cell (except AT50)

### Finials




### Mountings


Consult the eCatalog for details and the complete line of mountings.




CRA



CRC




CRD



CRF

### Poles and Pole Options

Consult the eCatalog for details and the complete line of poles.



RTA906/907

SSM8

RTA400

R80-TBC1

# AT10-20-30-40-50 Ancestra

## Post Top and Pendant

### Assembly examples

