

Project: _____


Location: _____

Cat.No: _____

Type: _____

Lamps: _____ Qty: _____

Notes: _____



Ordering Guide

Example: 32470 ABS U D 50H E N N G A

Product Code	32470	Grosse Pointe
Finish	ABS ACP ARD ASI BLK BRN BRZ FGN GRA IRN RBZ SRT VBZ VCP VGN VTC WBZ WHT	Antique Brass Antique Copper Antique Red Antique Silver Black Brown Bronze Forest Green Granite Ironstone Rustic Bronze Shadow Rust Verde Bronze Verde Copper Verde Vintage Copper Weathered Bronze White
Panel/Globe	U T	Lg. Clear Textured Polycarbonate w/ Spun Top Lg. Clear Textured Polycarbonate
Socket	D	Medium
Wattage/Source	50H 70H 35S 50S 70S 10S 10I	50W MH 70W MH 35W HPS 50W HPS 70W HPS 100W HPS 100W INC
Voltage	E F G H	120V 208V 240V 277V
Distribution	N A	None 4" Type V - Reflector Bowl
Photoeye	N	None
Cage	G V N	Grosse Pointe Perforated Band None
Finial	A M P N	Acorn Maple Leaf Grosse Pointe None

32470 Grosse Pointe

Post top

Specifications

CONSTRUCTION:

Cast aluminum finial. Spun aluminum roof. Four-piece die-cast aluminum top ring bolted to four-piece die-cast aluminum legs. Cast aluminum fluted ballast pod / fitter. Fitter slips over 3" O.D. post or tenon.

FINISH:

Resilient TGIC thermoset polyester powdercoat paint is electrostatically applied to every fixture. Specially formulated for Philips Outdoor Lighting, it provides UV protection, and the highest temperature rating in the industry. In addition to the standard color choices shown, a spectrum of custom colors is available.

PANELS/LENS/GLOBE:

See lenses for available options.

LAMPING:

Lamp is not included.

ELECTRICAL ASSEMBLY:

Lantern will be prewired and tested. All electrical components are ETL listed.

BALLAST:

Ballast and component parts mounted inside two-piece cast aluminum moisture proof ballast compartment. (Customer must specify wattage and voltage desired.)

MOUNTING:

Fixture mounts to 3" dia. post or tenon.

WARRANTY:

Three-year limited warranty.

CERTIFICATIONS:

ETL Listed to U.S. safety standards for wet locations. cETL Listed to Canadian safety standards for wet locations.

Height:

between 25 3/8" & 29 3/8"

Width:

between 11 1/2" & 13"

Fitter:

3" I.D.

EPA:

1.22 & 1.26 & 1.36

Max. Weight:

32 lbs.

