

Project: _____


Location: _____

Cat.No: _____

Type: _____

Lamps: _____ Qty: _____

Notes: _____



Ordering Guide

Example: 3176 R ABS U D 50H E P B G M

Product Code	3176	Grosse Pointe
Fitter	R	Ribbed
Finish	ABS ACP ARD ASI BLK BRN BRZ FGN GRA IRN RBZ SRT VBZ VCP VGN VTC WBZ WHT	Antique Brass Antique Copper Antique Red Antique Silver Black Brown Bronze Forest Green Granite Ironstone Rustic Bronze Shadow Rust Verde Bronze Verde Copper Verde Vintage Copper Weathered Bronze White
Panel/Globe	U	Lg. Clear Textured Polycarbonate w/ Spun Top
Socket	D G	Medium Mogul
Wattage/Source	50H 70H 10H 15H 35S 50S 70S 10S 15S 15I	50W MH 70W MH 100W MH 150W MH 35W HPS 50W HPS 70W HPS 100W HPS 150W HPS 150W INC.
Voltage	E F G H	120V 208V 240V 277V
Distribution	P	Type V - Cutoff Optics
Photoeye	B N	Button Eye None
Cage	G N	Grosse Pointe None
Finial	M N	Maple Leaf None

3176 Grosse Pointe

Post top

Specifications

CONSTRUCTION:

Cast aluminum finial. Spun aluminum top dome secures to globe. Type V Cut-Off Reflector system concealed by top dome.

FINISH:

Resilient TGIC thermoset polyester powdercoat paint is electrostatically applied to every fixture. Specially formulated for Philips Outdoor Lighting, it provides UV protection, and the highest temperature rating in the industry. In addition to the standard color choices shown, a spectrum of custom colors is available.

PANELS/LENS/GLOBE:

Clear ripple textured polycarbonate globe U.V. stabilized.

LAMPING:

Lamp is not included.

ELECTRICAL ASSEMBLY:

Lantern will be prewired and tested. All electrical components are ETL listed.

BALLAST:

Two piece cast aluminum watertight ballast compartment with 16 flutes. (Customer must specify ballast wattage and voltage required.)

MOUNTING:

Fixture mounts to 3" dia. post or tenon.

WARRANTY:

Three-year limited warranty.

CERTIFICATIONS:

ETL Listed to U.S. safety standards for wet locations. cETL Listed to Canadian safety standards for wet locations.

Height:

38 1/8"

Width:

15 5/8" or 17 1/8"

Fitter:

3" I.D.

EPA:

1.26 or 2.30 or 2.35

Max. Weight:

32 lbs.

