

Shaper

DESCRIPTION

The 161 series is a decorative wall sconce family with half rectilinear form. This product is a half square column shape shade, and also has rectangular shade in shade options, with a variety of options to highlight elegant spatial forms. The integral LED light engine is available in 2700K, 3000K, 3500K, and 4000K color temperatures that evenly illuminates the shade and the bottom lens, and 83+ CRI. Shaper's Fabrique collection is known for its high quality hand tucked fabrics. Heavy gauged steel frame, laminated styrene backing, and minimum internal structure. Shades come in three standard sizes, eleven standard fabrics, three vinyl materials, four printed wood patterns, and two translucent organza fabrics, allowing the designer to select a look for any space.

SPECIFICATION FEATURES

Construction

Aluminum housing, cold rolled steel cover and bracket extensions with LED boards attached. Optional matte white acrylic top cover available (TC).

161-25

Standard length = 25" OAH (Overall Height)

161-37

Standard length = 37" OAH (Overall Height)

161-49

Standard length = 49" OAH (Overall Height)

Shades

Aluminum wire frame painted white. Material backed on to heavy translucent white styrene. All shades have "Hand-Tucked Rolled Edges" except for Vinyl.

Fabric Shade Selections

SIW - Silk White
SIY - Silk Ivory
SWH - Shantung White
SEG - Shantung Eggshell
SBG - Shantung Beige
GBB - Glynn Brussels Beige
LOLA - Lola Sand
NGS - Nutmeg Shimmer
LCK - Linen Chopstick
LAT - Linen Alabaster
VLW - Verona Linen White

Vinyl Coated Fabric

ABR - Alabaster Vinyl
NFX - Natural Flax
GHY - Golden Honey
Note: not available for 49"

Printed Woods

PVDB - Varigated Bamboo
PMA - Maple
PCH - Cherry
PWA - Walnut

Note: For humid environments, such as showers or open lobbies, Vinyl Coated Fabrics are recommended. Not available for 49"

Organza Outer Shade Options

EDT - Earth Dust
WMT - White Mist

Electrical

Standard driver is electronic universal voltage (120-277V, 50/60 Hz), greater than 0.9 power factor, less than 20% harmonic distortion, and ambient temperatures of 25°C (77°F).

Control

Standard driver is 0-10V with 10% dimming.

Compliance

Components are UL recognized and luminaires are cUL listed for 25° ambient environments. Fixtures are rated for damp location listing. Made in North America.

Catalog #		Type
Project		
Comments		Date
Prepared by		

Cooper Lighting Solutions certifies that its products satisfy the requirements of ARRA Section 1605 of the American Recovery Reinvestment Act. All LED components are RoHS compliant and drivers conform to appropriate FCC regulations. Sconce products meet ADA regulations.

Life and Warranty

Standard five-year warranty on all parts.



161-W Series LED

Surface
Decorative LED Wall Sconce

cULus - 1598
Damp Location
LM79/LM80 Compliant

Length 25"

- Delivered Lumens (@3500K) 1962
- Wattage: 22W
- CRI: 80
- CCT: 2700K, 3000K, 3500K, 4000K

Length 37"

- Delivered Lumens (@3500K) 2828
- Wattage: 32W
- CRI: 30
- CCT: 2700K, 3000K, 3500K, 4000K

Length 49"

- Delivered Lumens (@3500K) 3871
- Wattage: 42W
- CRI: 80
- CCT: 2700K, 3000K, 3500K, 4000K

ORDERING INFORMATION (SELECT FIXTURE NUMBER AND SHADE NUMBER TO COMPLETE SPECIFICATION)

Fixture Number: 161-25-W-L3/827-UNV

Series ¹	Size	Mounting Type	LED Lamp			LED Voltage	Options ²
			25"	37"	49"		
161 = Square Rectilinear Wall Sconce	25"	W = Wall				UNV = (120-277V)	TC = Matte White Acrylic Top Cover RBP = Remote Battery Pack
	37"		L3/827	L4/827	L5/827		
	49"		L3/830	L4/830	L5/830		
			L3/835	L4/835	L5/835		
			L3/840	L4/840	L5/840		


Notes: ¹Fabric Kit is not included. Please specify Fabric Kit (below) to complete specification. ² 5' Max Mounting Distance.

Shade Number: 161-25-SHD-SIW

Series	Size	Shade	Finish			Options
161 = Square Rectilinear Shade	25"	SHD = Shade Fabric	Fabric: ^{1,2,3} SIW = Silk White SIY = Silk Ivory SWH = Shantung White SEG = Shantung Eggshell SBG = Shantung Beige GBB = Glynn Brussels Beige	LOLA = Lola Sand NGS = Nutmeg Shimmer LCK = Linen Chopstick LAT = Linen Alabaster VLW = Verona Linen White	Vinyl: ^{1,2} ABR = Alabaster Vinyl NFX = Natural Flax GHY = Golden Honey	Organize Shade in Shade WSQIS-EDT = Earth Dust WSQIS-WMT = White Mist
	37"					
	49"					

Notes: ¹Available for 25", ²Available for 37", ³Available for 49"

DIMENSIONS - SINGLE SHADE



DIMENSIONS - SHADE IN SHADE

