


3 3/4" (95mm) aperture  
Line Voltage 120V ES16 ESD16  
Standard Frame-In-Kit (Non-IC)

**Lytecaster**  
Recessed Downlight

# 302ESX



Complete fixture consists of Reflector Trim & Frame-in Kit. Select each separately

POWER PACK	CUT-OUT
302ESX	3 3/4" (95mm)

REFLECTOR TRIM
Accepts most 3 3/4" (95mm) 300 serie trims ; see Reflector Trim specification sheets.

## Features

**Mounting Frame** : 20ga. galvanized steel. Four slots are positioned 90° apart to simplify alignment.

**Mounting Bars**: (4) 18 ga. galvanized steel. 13" (330mm) long bars extend to 27" (686mm), rotatable and lockable, integral T-bar tabs. Spike detail eliminates the need of additional nailing.

**Mounting Bars Locking Clip** : (1) locks mounting bars in place.

**Snap-on Socket Cup** : 22ga. galvanized steel. Easy snap-on to housing.

**Socket** : Porcelain body ; Twist and lock (GZ base) Pre-wired with 18 ga. Teflon 250° leads to junction box.

**Junction Box** : 4"(102mm) x 3"(76mm) x 2"(51mm) 18 ga. galvanized steel . CSA/UL certified for maximum of 8 No. 12 ga. 90° C through branch circuit conductors. Integral cable clamp permit attachment of non metallic Loomex without need of additional connectors. Pry-out knock-outs accept BX cable. Easy access from both sides with snap-on covers.

**Thermal Protector** : Meets CSA/UL requirements. Insulation, if used, must be kept 3" (76mm) away from luminaire sides and junction box.

## Accessories

**Mounting Bars Extenders** : 1964

20" (508mm) long. Set of 2

**Mounting Bar Locking Clips** : 0098

To lock mounting bars in place after installation. Set of 12.

**Labels** : CSA , UL

Damp or Wet location rated depending on trim used.